



Sensors > Humidity Sensors > Humidity Sensor Assemblies > Humidity Temperature Transducer



Humidity Sensor Product Type: **RHT Module**

Supply Voltage (Peak): **12 VDC**

Operating Temperature Range: **-40 – 85 °C**

Accuracy: **±3 %RH**

Nominal Output @55%RH (at 5 VDC): **2.48 V**

[All Humidity Temperature Transducer \(1\)](#)

Features

Product Type Features

Humidity Sensor Product Type	RHT Module
Interface Signal Type	Analog

Electrical Characteristics

Supply Voltage (Peak)	12 VDC
Nominal Output @55%RH (at 5 VDC)	2.48 V
Current Consumption	1 mA
Output Impedance	70 Ω

Usage Conditions

Humidity Operating Range	0 – 100 %RH
Operating Temperature Range	-40 – 85 °C
Accuracy	±3 %RH
Sensitivity	26 mV/%RH

Other

Response Time	10 seconds
---------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: 4,4'-isopropylidenediphenol (Bisphenol A) (1% in Component) Dodecamethylcyclhexasiloxane (D6) (.5% in Component) Formamide (.2% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # HPP809A031
RH/T HTM2500LF TRANSDUCER



TE Part # HPP805A031
HM1500LF HUMIDITY MODULE



TE Part # HPP801A031
HS1101LF HUMIDITY SENSOR

Also in the Series | MEAS HTM2500LF



Humidity Sensor Assemblies(1)

Customers Also Bought



TE Part #DTMH04-2PA
REC, 2P, BLK, N, HI TEMP, A



TE Part #1-6609101-1
PSOSXS000=C1011




TE Part #3-1393117-0
KUP-11A55-24=KU



TE Part #4-2213767-3
AV19 DPM 3A MOVE RING LED
WHITE 24V




TE Part #449582-000
VERSAFIT-MINI-SPL-3/4-BK




TE Part #2-2176528-3
3503G 2B 10K 1% 5K RL




TE Part #953440-5
6W MOS HEADER BENT RIGHT



TE Part #1614960-8
CPF 0805 1R0 0.1% 25ppm 5K RL



TE Part #3-1614958-1
CPF 0805 2R0 0.1% 25ppm 1K RL



TE Part #1-1670194-1
CABLE FIXATION

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HPP809A033_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HPP809A033_D.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_HPP809A033_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HTM2500LF-HUMIDITY](#)

English