



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: Cable Clamp

Number of Positions: 9

UL Flammability Rating: UL 94V-0

Packaging Method: Bag

Packaging Quantity: 500

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp
------------------------------	-------------

Configuration Features

Number of Positions	9
---------------------	---

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	500

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 172161-1
9 CIR UNIV M-N-L CAP



TE Part # 794370-1
08P MINI UMNL STR RELIEF HNGD



TE Part # 1-172161-9
MINI UNIVERSAL M-N-L CAP 9P

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(89)



Connector Hardware(4)



Connector Seals & Cavity Plugs(17)



Connector Strain Relief(2)



Insertion & Extraction Tools(1)




Rectangular Power Connectors(197)

Customers Also Bought



TE Part #1-1903128-0
DYNAMIC 1100D TAB HSG 40P P/M



TE Part #170365-3
MINI UNIVERSAL M-N-L SOCKET LP



TE Part #172161-1
9 CIR UNIV M-N-L CAP



TE Part #172169-1
9 CIR UNIV M-N-L PLUG




TE Part #2-1625931-9
MCU 2K2 10% 1" PL



TE Part #1825516-2
MSP103C04



TE Part #DT04-12PA-E003
REC, 12P, GRY, N, CAP, A



TE Part #170363-3
MINI UNIVERSAL M-N-L PIN LP

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_316455-1_A_c-316455-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_316455-1_A_c-316455-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_316455-1_A_c-316455-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English



[Product Specifications](#)

[Application Specification](#)

English