




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **5180 – 13100 CMA**
Stud Size: **#10**

Features

Product Type Features

Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.99 mm[.039 in]
Product Length	19.74 mm[.777 in]
Barrel Inside Diameter	3.28 mm[.129 in]



Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	2500
Packaging Method	Tape Mounted

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 58545-1 SOLISTRAND 10-22 DIE ASSY	 TE Part # 49935 DAHT SOLIS 22-10 ASSY	 TE Part # 58546-1 PC 22-10 SOLISSPICE SPL I SHT	 TE Part # 58545-3 SDE DIE ASSY. 22-10 SOLISTRAND
--	--	--	---

Customers Also Bought

 TE Part #1-640251-2 12P SL156 HSG W/O LCK RAMP	 TE Part #52420-3 TERMINAL,PIDG SPR SPD 16-14 6	 TE Part #2-35772-1 TERMINAL,SOLIS R 12-10 1/4	 TE Part #2-34113-2 SOLIS R 22-16COMM 22-18MIL 1/4
 TE Part #53120-2 SOLIS SP SPD 22-16COM22-18MIL6	 TE Part #8-1437657-0 8PCV-04-006=#8 TRIBARRIER	 TE Part #53832-2 SOLIS SP SPD22-16COM22-18MIL10	 TE Part #53833-2 TERMINAL,SOLIS SPR SPD 16-14 8
 TE Part #6-1879350-3 RR01 5% 82R AMMO	 TE Part #2-34112-2 SOLIS R 22-16COMM 22-18MIL 10		

Documents

Product Drawings

TERMINAL,SOLIS SPR SPD 12-10

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_53836-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53836-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53836-2_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_53836-2_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_53836-2_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_53836-2_C.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English