



IMPACT

TE Internal #: 2007711-1
144 Position, Mating Alignment, Polarization Mating Alignment
Type, 9 Row, 16 Column, PCB Mount Receptacle, IMPACT, High
Speed Backplane Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 144
Row-to-Row Spacing: 1.35 mm [.053 in]
Mating Alignment: With
Mating Alignment Type: Polarization
Number of Rows: 9

Features

Product Type Features

Signal Arrangement	Differential
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded

Configuration Features

Number of Ground Positions	48
Number of Pairs	48
Stackable	No
Number of Signal Positions	96
Number of Positions	144
Number of Rows	9
Number of Columns	16
PCB Mount Orientation	Right Angle
Guide Location	Unguided

Electrical Characteristics

Impedance	100 Ω
Operating Voltage	30 VAC



Signal Characteristics

Number of Differential Pairs per Column	3
Data Rate	20 – 25 Gb/s

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	1.27 µm[50 µin]
Contact Layout	Inline
Contact Type	Socket
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.762 µm[30 µin]
Contact Mating Area Plating Material	Gold
Contact Shape & Form	Dual Beam
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	.75 A

Termination Features

Termination Post & Tail Length	1.2 mm[.047 in]
Termination Method to PCB	Through Hole - Press-Fit

Mechanical Attachment

Guide Hardware	Without
Mating Retention	Without
PCB Mount Retention	With
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
Mating Alignment Type	Polarization
Connector Mounting Type	Board Mount

Housing Features

Number of Shrouded Sides	0
Housing Material	LCP - GF (Liquid Crystal Polymer)
Centerline (Pitch)	1.9 mm[.075 in]



Dimensions

Connector Length	30.4 mm[1.197 in]
Connector Height	13.3 mm[.524 in]
Connector Width	24.2 mm[.953 in]
PCB Thickness (Recommended)	1 mm
PCB Hole Diameter	.39 mm[.015 in]
Row-to-Row Spacing	1.35 mm[.053 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Box & Tube, Package
------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability











Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2007804-1 IMP100S,H,V3P16C,UG,OEW39,4.5	 TE Part # 2007809-1 IMP100S,H,V4P10C,LG,OEW39,4.5	 TE Part # 2007813-1 IMP100S,H,V4P10C,RG,OEW39,4.5	 TE Part # 2007793-1 IMP100S,H,V3P16C,LG,OEW39,4.5
 TE Part # 2007806-1 IMP100S,H,V3P16C,UG,DEW39,4.5	 TE Part # 2007807-1 IMP100S,H,V3P16C,UG,REW39,4.5	 TE Part # 2007811-1 IMP100S,H,V4P10C,LG,REW39,4.5	 TE Part # 2007815-1 IMP100S,H,V4P10C,RG,LEW39,4.5
 TE Part # 2007820-1 IMP100S,H,V4P10C,UG,OEW39,4.5	 TE Part # 2007821-1 IMP100S,H,V4P10C,UG,LEW39,4.5	 TE Part # 2007793-2 IMP100S,H,V3P16C,LG,OEW39,4.9	 TE Part # 2007795-1 IMP100S,H,V3P16C,LG,REW39,4.5
 TE Part # 2007805-1 IMP100S,H,V3P16C,UG,LEW39,4.5	 TE Part # 2007811-2 IMP100S,H,V4P10C,LG,REW39,4.9	 TE Part # 2007813-2 IMP100S,H,V4P10C,RG,OEW39,4.9	 TE Part # 2007815-2 IMP100S,H,V4P10C,RG,LEW39,4.9



TE Part # 2007816-2
IMP100S,H,V4P10C,UG,OEW46,4.9



TE Part # 2007816-3
IMP100S,H,V4P10C,UG,OEW46,5.5




TE Part # 2007817-3
IMP100S,H,V4P10C,UG,LEW46,5.5



TE Part # 2007820-2
IMP100S,H,V4P10C,UG,OEW39,4.9

Also in the Series

IMPACT



High Speed Backplane Connectors
(1318)


Customers Also Bought




TE Part #2149730-1
SFP+ 1x4 Cage, Heatsinks and Lightpipes



TE Part #5787013-1
8 CIRC DIN RCPT W/GRND FINGERS



TE Part #1-2338987-1
QSFP28, 1X3, CAGE ASSY, SPRING, HS, LP



TE Part #1-2345015-1
CAGE ASSY, QSFP28 1X1, SPRING, HS, LP



TE Part #6766497-1
CONNECTOR, SOCKET, STRAIGHT, COMPLIANT,



TE Part #1-2007798-3
IMP100S,H,V3P16C,RG,LEW46,5.5



TE Part #2030532-1
SWITCH, 3 WIRE CONNECTION, 3 M LEAD WIRE



TE Part #2127367-1
C/A, MOTO 30009314001, A-MITE, DB-25



TE Part #2382940-1
CA,MBXLE TO MINI-FIT AND PCB HEADER



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_2007711-1_D.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2007711-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2007711-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[7-1773458-1_IMPACT_BACKPLANE_CONNECTOR_SYSTEM_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English