




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2.08 – 5.26 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Silver
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.46 mm[.018 in]
Product Length	19.18 mm[.755 in]
Compatible Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Wire Size	2.08 – 5.26 mm ²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	9000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-SCH691-T1 PCB Power Relay: 30 Amp, Monostable DC	 TE Part # 1-1649341-7 T9CP5A54-24	 TE Part # 1649341-2 T9CP1A54-240	 TE Part # 1-1649341-9 T9CP5A54-120
 TE Part # 2-1649341-5 T9CP2A54-120	 TE Part # 1649341-5 T9CP1A52-120	 TE Part # 1649341-8 T9CP1A54-24	 TE Part # 1-1649341-2 T9CP5A52-24
 TE Part # 2-1649341-0 T9CP5A54-240	 TE Part # 1-521785-1 250 FASTON HSG.,REC.,2 POS, NATRUAL	 TE Part # 1649341-6 T9CP1A52-240	 TE Part # 1-1649341-0 T9CP1A54-120
 TE Part # 1-1649341-4 T9CP5A52-120	 TE Part # 1-1649341-5 T9CP5A52-240	 TE Part # 7-2150237-7 OCEAN_2.0_SPARE_PART_KIT- 130F2100	 TE Part # 2150237-1 OCEAN_2.0_APPLICATOR-E- 130F2100-REM



TE Part # 2150237-2
OCEAN_2.0_APPLICATOR-E-130F210O-REA

TE Part # 2-1649341-4
T9CP2A54-240

TE Part # 1-1649341-1
T9CP5A52-12

TE Part # 90120
DAHT 250 FASTON REC 14-10 ASSY

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(426)

Splices(4)

Customers Also Bought

TE Part #521367-1
ULTRA POD: Straight, Receptacle Assembly, Unplated, .250 inch

TE Part #61399-1
312 FASTON REC 16-12 AWG TPBR

TE Part #63306-2
250 FASTON REC 18-14 AWG TPBR

TE Part #63933-1
PL .250 TERMINAL REC 22-18 AWG BR

TE Part #521411-1
ULTRA-POD 250 ASY REC 22-18 AWG BR

TE Part #1742883-1
187 FASTON,REC.,20-16 AWG,NPST

TE Part #7-1241961-2
STD TIM HOUSING MKII 2POS

TE Part #2-176498-6
187 HSG. PL MKII REC. 15mm 2P BLUE



TE Part #5-1969536-4
HSG,RECP,POSILOK MKIII ,250SER,3P,
2CIR

Documents

Product Drawings

250 FASTON REC 14-10 AWG SPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63435-1_W.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63435-1_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63435-1_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English