



Terminals & Splices > Automotive Terminals > AMP MCP, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **2.8 mm** [.11 in]

Mating Tab Thickness: **.8 mm** [.031 in]

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **20 – 17 AWG**

[All AMP MCP, RECEPTACLE AND TAB \(110\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	15 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions



Compatible Insulation Diameter Range	1.3 – 2.1 mm[.051 – .083 in]
Wire Size	.5 – 1 mm²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	LV214
---	-------

Packaging Features

Packaging Quantity	4500
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2141029-1 FUSE BOX ASSY,HARD WIRED	TE Part # 2151164-1 OCEAN_2.0_APPLICATOR-S-080F100OV-RSM	TE Part # 2151164-2 OCEAN_2.0_APPLICATOR-S-080F100OV-RSA	TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp
TE Part # 5-2151164-1 OCEAN_2.0_APPLICATOR-S-080F100OV-RSM	TE Part # 5-2151164-2 OCEAN_2.0_APPLICATOR-S-080F100OV-RSA	TE Part # 7-2151164-7 OCEAN_2.0_SPARE_PART_KIT-080F100OV	

Also in the Series | AMP MCP 2.8

Automotive Connector Caps & Covers (1)	Automotive Connector Locks & Position Assurance(5)	Automotive Housings(162)	Automotive Terminals(53)



Connector Seals & Cavity Plugs(4)




Insertion & Extraction Tools(6)



Module Components(1)




Other Automotive Connector Accessories(1)



PCB Headers & Receptacles(1)

Customers Also Bought



TE Part #969005-3
MT2 A REC 1.6 Contact SWS Sn



TE Part #7-1452665-2
MCON 1.2 LL REC SWS AU



TE Part #2103177-1
PLUG ASSY, KEY A, TA,CPA, HVA280-2PHI XE



TE Part #1719661-1
2 LOCK REC HSG



TE Part #1563126-1
2. LOCK,10 POS MALE HOUSING



TE Part #1-2236269-2
24POS, MIXED,REC HSG, 20GENYMCP,ASSY,CODB



TE Part #2-2236896-1
2POS, MCON 1.2 LL REC SEALED



TE Part #2035334-8
CONTACT, FEMALE0.64 ,20.35SQMM



TE Part #4-2098269-6
10P Plug Assembly (2x5), Gener

Documents



Product Drawings

AMP MCP 2.8, CONTACT LANCELESS

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1355833-1_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1355833-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1355833-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MFINITY Modular Hard Wired Fuse and Relay Box

English

Product Specifications

Application Specification

English