




Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Horizontal Mount



Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **10 W**

Resistance Class: **Up to 1kΩ**

Resistance Value: **47 Ω**

[All Wirewound Resistor: Horizontal Mount \(157\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	10 W
Resistance Class	Up to 1kΩ
Resistance Value	47 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Radial-Leaded Pluggable
-----------	-------------------------

Termination Features

Termination Area Base Material	Steel
Number of Terminations	2

Dimensions

Passive Component Dimensions	48 x 10 x 10 mm
------------------------------	-----------------



Usage Conditions

Operating Temperature Range	-55 – 250 °C
Temperature Coefficient	±300 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-SQ1  
Wirewound Resistor: Vertical Mount

Also in the Series | CGS SQ

Through-Hole Resistors(662)

Customers Also Bought

TE Part #DTM04-12PB  
REC, 12P, BLK, N, B

TE Part #DT04-3P-C015  
DEUTSCH DT Receptacle Connectors

TE Part #1218266-1  
CONT,CRIMP PIN,18AWG,109,SZ 20

TE Part #206795-3  
AMPLIMITE,SKT CONT ASY,SZ 20

TE Part #1218267-1  
CONT,CRIMP SKT,18AWG,109,SZ 20

TE Part #0413-217-1605  
SEALING PLUG, SIZE 16, LOCKING, WHT

TE Part #171661-1  
E-J MK-2 070 TAB CONT

TE Part #1060-20-0222  
PIN, SF, SIZE 20, 16-22, NI/NI

TE Part #2205511-1  
CA MICRO-MATCH MOW MOW 16 POS



Documents

Product Drawings

[SQZ10 47R 5%](#)

English

Datasheets & Catalog Pages

[4-1773460-6\\_RESISTIVE\\_SOLUTIONS\\_RAIL](#)

English

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[High Power Resistors - Type SQ Series](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English