

3-Port Metal DIN-Rail Mounting Module for Snap-In Keystone Jacks and Couplers, Silver, TAA

MODEL NUMBER: N063-003



Accepts snap-in keystone jacks and couplers to help you manage your DIN-rail network cable application.

Features

Organizes a Wide Variety of Ethernet Network Patch Cables in Your DIN-Rail Installation

This DIN-rail mounting module lets you manage network cable interconnectivity with three blank cutouts, which accommodate all snap-in keystone jacks and in-line couplers. Made from sheet metal with nickel plating, the N063-003 is quick and easy to install on a standard 35-millimeter DIN rail using the built-in mounting clip.

TAA-Compliant for GSA Schedule Purchases

The N063-003 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332276889
Technology	Cat5/5e; Cat6; Cat6a
Firmware / Software Docs	
Offset Ports	No
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	(3) KEYSTONE JACK CUTOUT
PHYSICAL	
Primary Form Factor	DIN-Rail

Highlights

- Heavy-duty metal construction ideal for industrial Ethernet network applications
- 3 blank cutouts compatible with all keystone jacks and couplers
- Built-in mounting clip attaches to standard 35 mm DIN rail with no tools needed
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

N063-003 Metal DIN-Rail Mounting Module, 3 Ports



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Silver
Material of Construction	SUS304 & SPCC NI PLATE (STEEL)
Total Number of Ports	3
Shipping Dimensions (hwd / in.)	2.10 x 4.50 x 8.00
Shipping Weight (lbs.)	0.15
Unit Dimensions (hwd / in.)	2.120 x 1.940 x 2.380
ENVIRONMENTAL	
Operating Temperature Range	-13° to 122°F (-25° to 50°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 85% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
All-in-One Kit	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Numbered Ports	No
DIN Mountable	Yes
Keystone Jacks	Yes
Built-in Cables	No
Color-Coded Connections	No
EIA/TIA 2/32 Spacing	No
Labeled Ports	No
Down-Angled Ports	No
Panel Applications	Ethernet
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.