

CIRHSE06T16S1SCNF80M32V0

✕ OBSOLETE

TE Internal #: Y5015-000000100004

TE Internal Description: FREE SOCKET CONNECTOR

Plug with RFI Grounding - Female - CIRH

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Plug with RFI Grounding - Female - CIRH



Connector System: **Cable-to-Cable, Wire-to-Wire**

Number of Positions: **7**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

Reverse Gender: **Yes**

Features

Product Type Features

Product Type	Connector Assembly
Accessory Color	Black
Prewired	No
Connector System	Cable-to-Cable, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Factory Installed Backshell	Without
Number of Positions	7
Contacts Preloaded	No

Body Features

Shell Plating Material	Black Chromate Over Zn Cobalt
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Low Fire Hazard Rubber

Contact Features

Reverse Gender	Yes
Contact Layout Arrangement	16 – 1



Circular Connector Contact Type	Socket
---------------------------------	--------

Mechanical Attachment

Mating Retention Type	Bayonet
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With

Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]

Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

Packaging Features

Packaging Quantity	10
--------------------	----

Other

Position Locations Omitted	All
Field Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #2-966067-1
FER,WIRE,PL SLV,4.00/12,L18,GREY,LP




TE Part #1-2176345-4
CRGCQ 1210 120R 1%




TE Part #2176326-4
CRGP 0603 18R 1%




TE Part #ZPF000000000000358
006-0937-12 A




TE Part #ZPF000000000000335
006-0912-12 A




TE Part #ZPF00000000000033222
983-0S 14-04 PN-L




TE Part #8-1879334-1
CPF 0603 13R7 1% 50PPM 1K RL



TE Part #Y5015-000000100125
FIXED PIN CONNECTOR



TE Part #Y5015-000000100131
FIXED PIN CONNECTOR



TE Part #A96584-000
82A0113-10-9-F874

Documents

Product Drawings
FREE SOCKET CONNECTOR

French

Datasheets & Catalog Pages
CIRH Brochure

English



Product Specifications

Application Specification

French