

DTHD04-1-4P-E003

✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTHD

TE Internal #: DTHD04-1-4P-E003

Housing for Male Terminals, Wire-to-Wire, 1 Position, Sealable, Black, Wire & Cable, Power, Cable Mount (Free-Hanging), Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTHD Housings



Connector System: **Wire-to-Wire**  
Number of Positions: **1**  
Connector & Housing Type: **Housing for Male Terminals**  
Sealable: **Yes**  
Mating Pin Diameter: **5.72 mm [ .225 in ]**

[All DEUTSCH DTHD Housings \(14\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Connector Modification	End Cap
Number of Positions	1
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Nominal Voltage Architecture	250 V
------------------------------	-------

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 4
Contact Type	Pin
Mating Pin Diameter	5.72 mm[.225 in]
Contact Current Rating (Max)	100 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	With
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PEI (Polyetherimide)
------------------	----------------------

Dimensions

Connector Height	43.18 mm[1.7 in]
Product Width	26.54 mm[1.045 in]
Product Length	53.8 mm[2.118 in]
Compatible Insulation Diameter Range	6.63 – 10.67 mm[.261 – .42 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	Not Tested
UL Flammability Rating	Not tested

Packaging Features

--	--



Packaging Quantity	500
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-PCH8172  
DEUTSCH DTHD Housings



TE Part # 0460-204-0490  
PIN, SOLID, SIZE 4, 6AWG, NI



TE Part # CAT-D487-M8649  
DEUTSCH DT Mounting Clips



TE Part # 1924487-2  
MOUNTING CLIP, AMPSEAL 16



TE Part # 114019-ZZ  
SEALING PLUG, SIZE 4, WHT




TE Part # 114009-ZZ  
EXT TOOL, SIZE 4, 6 AWG, N, WHT


Also in the Series | **DEUTSCH DT**




Automotive Connector Caps & Covers  
(19)




Automotive Connector Locks &  
Position Assurance(87)



Automotive Housings(706)




Connector Backshells(61)




Connector Seals & Cavity Plugs(6)



Connector Strain Relief(28)



Insertion & Extraction Tools(3)



Other Automotive Connector  
Accessories(28)



PCB Headers & Receptacles(106)

Also in the Series | **DEUTSCH DTHD**



Automotive Housings(22)



Other Automotive Connector Accessories(1)

### Customers Also Bought



TE Part #DRC16-70SBE-P013  
DEUTSCH DRC Housings



TE Part #0460-204-0490  
PIN, SOLID, SIZE 4, 6AWG, NI




TE Part #DT06-3S-CE04  
PLG, 3P, GRY, E, XCAP



TE Part #DTHD04-1-8P-E003  
DEUTSCH DTHD Housings



TE Part #DT04-12PB-CE07  
REC, 12P, BLK, E, ENH KEY, CAP, B



TE Part #963357-6  
2X 2P MESSERLEISTE

### Documents

#### Product Drawings

REC, 1P, BLK, N, SIZE 4, CAP

English

#### CAD Files

Customer View Model

ENG\_CVM\_CVM\_DTHD04-1-4P-E003\_99.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_DTHD04-1-4P-E003\_99.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_DTHD04-1-4P-E003\_99.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.





---

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

---

Product Specifications

Application Specification

English