



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #185311-1
6POS MQS REC

TE Part #1-1473562-4
RITS CONN. PLUG ASSY 4P RED

TE Part #2-1473562-4
RITS CONN. PLUG ASSY 4P BLUE

TE Part #180941
FF 250 REC HSG 3P NYLON NAT

TE Part #7-1452656-1
MCON Receptacle and Tab

TE Part #BKA186N00480100000
923 EXTENSION, SPEEDTEC

TE Part #ESA002N00320001000
615 EXTENSION

TE Part #EKA201N00340500000
915 EXTENSION

TE Part #ESA201N00310500000
915 PLUG

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_EKA201N00320602000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_EKA201N00320602000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_EKA201N00320602000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

EKA201N00320602000

English



[fuer Datenblaetter, die online konfigurierbar sind](#)

German