



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Interface Seal**
Primary Product Material: **Urethane Foam**
Operating Temperature (Max): **90 °C [194 °F]**
Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Interface Seal
----------------------------	----------------

Body Features

Primary Product Material	Urethane Foam
--------------------------	---------------

Usage Conditions

Operating Temperature (Max)	90 °C[194 °F]
Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag/Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-770969-1 06P MINI UMNL R/A HDR ASSY LF	 TE Part # 794895-1 6 CIR MINI UMNL RND WIRE HOLES	 TE Part # 794940-1 06P MINI UMNL CAP HSG	 TE Part # 1-770969-0 06P MINI UMNL R/A HDR ASSY SN
 TE Part # 1-770875-0 06P MINI UMNL HDR ASSY SN	 TE Part # 794758-1 MINI UMNL WIRE SEAL,18-26AWG	 TE Part # 1586359-6 06P MINIMUMNL GANG WIRE SEAL DR	 TE Part # 770969-2 06P MINI UMNL R/A HDR ASSY AU





TE Part # 770875-2
06P MINI UMNL HDR ASSY VO AU



TE Part # 770875-1
06P MINI UMNL HDR ASSY SN

Also in the Series

Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(89)



Connector Hardware(4)



Connector Seals & Cavity Plugs(17)



Connector Strain Relief(2)



Insertion & Extraction Tools(1)



Rectangular Power Connectors(197)

Customers Also Bought



TE Part #794781-1
10P MINI UMNL PLUG HSG



TE Part #1-770969-0
06P MINI UMNL R/A HDR ASSY SN



TE Part #794805-1
4 CIR UMNL PLUG,ROUND HOLES



TE Part #794772-8
08P MINI UMNL SEAL,DIE CUT



TE Part #794894-1
02P MINI UMNL PLUGS WIRE HOLES




TE Part #794772-2
02P MINI UMNL SEAL,DIE CUT



TE Part #794758-1
MINI UMNL WIRE SEAL,18-26AWG



TE Part #1586359-6
06P MINIMUMNL GANG WIRE SEAL DR



Documents

Product Drawings

06P MINI UMNL SEAL,DIE CUT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794772-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_794772-6_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_794772-6_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English