



Terminals & Splices > Automotive Terminals > AMPSEAL 16 CONTACTS



Terminal Type: **Socket**
Mating Pin Diameter: 1.59 mm [.062 in]
Terminal Transmits: 0 – 24 A (Low Power)
Wire Size: .823 – 2.08 mm²

[All AMPSEAL 16 CONTACTS \(35\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	Size 16
Contact Fabrication	Stamped & Formed
Typical Current Rating	13 A
Crimp Type	F-Crimp
Terminal Type	Socket
Mating Pin Diameter	1.59 mm[.062 in]
Interface Plating	Gold (Au)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.95 – 3.94 mm[.077 – .155 in]
Wire Size	.823 – 2.08 mm²



Tab Length	18.23 mm[.718 in]
------------	-------------------

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	4000
Packaging Method	Package

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-AM7801-CH8172 AMPSEAL 16 Housings	 TE Part # CAT-H991-CH8172 AMPSEAL 16 Hybrid Lever Housings	 TE Part # 1924463-1 PIN, SF, SIZE 16, 18-20 AWG, AU/SN	 TE Part # 2151239-1 OCEAN_2.0_Applicator-S-100F-RSM
 TE Part # 2151239-2 OCEAN_2.0_Applicator-S-100F-RSA	 TE Part # 2217753-1 CCII SOCKET PIN CONT 18-14 ASSY	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151239-7 OCEAN_2.0_SPARE_PART_KIT-100F

Also in the Series | AMPSEAL 16

 Automotive Connector Caps & Covers (3)	 Automotive Connector Locks & Position Assurance(2)	 Automotive Housings(244)	 Automotive Terminals(35)
 Connector Backshells(84)	 Connector Seals & Cavity Plugs(4)	 Data Connectivity Headers(2)	 Data Connectivity Housings(3)



Other Automotive Connector
Accessories(11)

Customers Also Bought



TE Part #776427-1
AMPSEAL 16 Housings



TE Part #160860-4
FF 250 REC 0.5-1.0MM2 TPPB




TE Part #280311
IS 375 FASTON NYLON



TE Part #DT04-12PA-BE03
REC, 12P, BLK, N, ENH KEY, CAP, A




TE Part #2-2109432-2
PCU SLD 105P PLUG ASSY(B-LH) I



TE Part #1-929504-3
2X 4P JUN-POW-TIMGH



TE Part #2209544-9
60P,PLUG ASSY,NORMAL CODING



TE Part #2341467-1
REC CONN CVR,39POS,AMP MCP 2.8, LOW BRKT



TE Part #3-967624-6
JUN-POW-TIM GEH 18P

Documents

Product Drawings

SOC, SF, SIZE 16, 14-18 AWG,NO INS,AU/SN

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_776491-1_B.3d_igs.zip



English

Customer View Model

[ENG_CVM_776491-1_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_776491-1_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English