

CRGCQ1210F120K

✓ ACTIVE

Neohm | Neohm CRGCQ

TE Internal #: 5-2176345-0

General Purpose Resistor, Thick Film, 1210, .5 W, 120K ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRGCQ

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: General Purpose Resistor

Element Type: Thick Film

Package Size Code: 1210

Power Rating: .5 W

Resistance Value: 120K Ω

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	1210

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.5 W
Resistance Value	120K Ω
Resistance Class	1kΩ – 1MΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]



Product Width	2.6 mm[.102 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRCGQ1210F120K

General Purpose Resistor, Thick Film, 1210, .5 W, 120K ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRCGQ



TE Part # 1-2176341-7
CRCGQ 0805 220R 1%

TE Part # 1-2176345-2
CRCGQ 1210 82R 1%

TE Part # 1-2176347-7
CRCGQ 2010 220R 1%

TE Part # 2176349-4
CRCGQ 2512 18R 1%

TE Part # 1-2176350-2
CRCGQ 2512 68R 5%

Also in the Series | Neohm CRCGQ

Surface Mount Resistors(728)

Customers Also Bought

TE Part #1-1623782-2
SQM5 470R 5% (METAL FILM)

TE Part #2-1623730-7
BCHE 4 W 6R8 10%

TE Part #2309411-1
DDR4 SODIMM 260P 8.0H STD

TE Part #1-1571983-0
GDH08S04=DIP SWITCH

TE Part #2007194-1
SFP+ 1x1 Cage Assembly, PCI, Solder Tail

TE Part #9-1614882-1
CPF 0603 10R 0.1% 25PPM 1K RL

TE Part #42822-2
250 FASTON TAB TPBR

TE Part #F55931-000
1966-RIBBON

CRGCQ1210F120K

General Purpose Resistor, Thick Film, 1210, .5 W, 120K ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRGCQ



TE Part #224151-E
M8 FEMALE, A CODE, 4P, 16.25MM
SMT

Documents

Product Drawings

CRGCQ 1210 120K 1%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2176345-0_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2176345-0_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2176345-0_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CRGCQ Data Sheet

English