




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.3 mm[.012 in]
Product Length	14.86 mm[.585 in]
Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Wire Size	.51 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	20000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63477-2 187 FASTON REC 20-16 AWG TPBR	 TE Part # 63477-6 187 FASTON REC 20-16 AWG TPBZ	 TE Part # 2150007-1 OCEAN_2.0_Applicator-E-090F140F-REM	 TE Part # 91509-1 CCII FASTON 187 REC 20-16 ASSY
 TE Part # 2150007-2 OCEAN_2.0_Applicator-E-090F140F-REA	 TE Part # 2232975-1 187 FASTON,REC.,20-16 AWG,TPBR	 TE Part # 7-2150007-7 OCEAN_2.0_SPARE_PART_KIT-090F140F	 TE Part # 2825538-1 MAG-MATE 25-22 187 FTAB TPBR

Also in the Series | FASTON 187

 Crimp Terminal Housings(41)	 Insertion & Extraction Tools(1)	 Joints & Splices(1)	 PCB Terminals(42)
---------------------------------	-------------------------------------	-------------------------	-----------------------




Quick Disconnects(208)



Splices(1)

Customers Also Bought



TE Part #1376391-1
5MM POWER KEY 6P PLUG HSG NUT




TE Part #1376396-1
Power Key TPA



TE Part #1971786-2
PTL TAB CONTACT, 20 - 24 AWG



TE Part #1971237-2
PTL RECEPTACLE CONTACT, 2X20 AWG



TE Part #360010-1
187 FASTON HSG.,REC.,3 POS, NATRUAL



TE Part #62137-2
187 FASTON REC 20-16 TPBR



TE Part #62754-1
SPLICE 14000-30000 .030 BR



TE Part #63539-1
250 FASTON REC 14-10 AWG TPBR

Documents

Product Drawings

187 FASTON REC 20-16 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_60214-1_AA.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60214-1_AA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60214-1_AA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Hand Crimping Tool 90180-2

English

Agency Approvals

UL Report

English