



Sensors > Temperature Sensors > RTD Sensors > RTD Probes > Stator (Rear Exit) RTD, CTO Mod 300H



RTD Sensor Type: **Stator**
Element Type: **Fiberglass Body**
Element Material: **Copper**
Lead Wire Style: **Standard PTFE**
Operating Temperature (Max): **180 °C [356 °F]**

[All Stator \(Rear Exit\) RTD, CTO Mod 300H \(7\)](#)

Features

Product Type Features

RTD Sensor Type	Stator
Element Type	Fiberglass Body
Element Material	Copper
Lead Wire Style	Standard PTFE

Usage Conditions

Operating Temperature (Max)	180 °C[356 °F]
-----------------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (85% in Component) <small>Article Safe Usage Statements:</small>



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | MEAS 300 Series




Customers Also Bought







TE Part #806606-000
202A153-25-0




TE Part #1838893-2
M12 MtI MALE PNL CONN. Sldr Rear (Hex)




TE Part #1-66103-5
III+ PIN,24-20,TIN-LEAD,SMPACK




TE Part #878504-000
202K153-25-01-0




TE Part #806674-000
202D932-25-0




TE Part #R-7119
RTD,STRR,P100,385,.5%,.078T,H



TE Part #R-2428
RTD,SM,SR,P100,385,.5%,.06T



TE Part #R-10422-6
RTD,STRR,P100,385,.5%,.050T,H



TE Part #R-8204
RTD,STRR,P100,385,.5%,.030T,H

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_R-1802_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_R-1802_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_R-1802_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

TESS-ANDO-408-0000052

English