

EH3269-000

✓ ACTIVE

RAYCHEM

TE Internal #: EH3269-000

Black, 2:1, Single Wall Tubing, Shrinks To 20 mm [.789 in],
Elastomer, 40 mm [1.575 in] Inner Diameter, Highly Flame-
Retardant, Spool, -75 – 150 °C

[View on TE.com >](#)

Heat Shrink Tubing > Single Wall ZH 150: Heat Shrink Tubing, 2:1 Shrink Ratio



Primary Product Color: **Black**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **40 mm [1.575 in]**

Recovered Inside Diameter (Max): **20 mm [.789 in]**

Shrink Ratio: **2:1**

[All Single Wall ZH 150: Heat Shrink Tubing, 2:1 Shrink Ratio \(8\)](#)

Features

Product Type Features

Wall Type

Single Wall

Body Features

Material Systems Code

100, 25

Primary Product Color

Black

Shrink Ratio

2:1

Primary Product Material

Elastomer

Flexibility

Flexible

Dimensions

Expanded Inside Diameter (Min)

40 mm[1.575 in]

Recovered Inside Diameter (Max)

20 mm[.789 in]

Tubing Size Range

20 – 40 mm[.789 – 1.575 in]

Usage Conditions

Tubing Flammability Type

Highly Flame-Retardant

Operating Temperature Range

-75 – 150 °C

Recovery Temperature

175 °C

Operation/Application

Mechanical Resistance

Fluids

Packaging Features

Packaging Method

Spool

Other

Meets Low Outgassing Requirements

No

Product Source

Czech Republic

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



Documents

Product Drawings

[ZH150-40/20-0-SP](#)

English

Datasheets & Catalog Pages

[1654025_Sec3_ZH-100](#)

English

[raychem-tubing-product-selection-guide](#)

English

Product Specifications

[Installation instructions for ZH150 tubing](#)

English