



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 83700 – 119500 CMA

Stud Size: 5/16, M8

Features

Product Type Features

Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	5/16, M8
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Contact Features

Barrel Type	Closed
Terminal Orientation	45 Bend
Terminal Plating Material	Nickel

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	83700 – 119500 CMA
-----------	--------------------



Stud Diameter	8.33 mm[.328 in]
Tongue Thickness	1.78 mm[.07 in]
Product Length	40.74 mm[1.604 in]
Barrel Inside Diameter	11.28 mm[.444 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	343 °C[649 °F]

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer










This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 <p>TE Part # 1490414-3 HYP10 SOLIS HD 1/0AWG INDENTER</p>	 <p>TE Part # 601075 BANTAM ROTA-CRIMP TOOL</p>	 <p>TE Part # 1490413-5 HYP10 SOLIS 1/0AWG NEST</p>	 <p>TE Part # 45436 HYP8/10 SOLIS 1/0AWG DIE SET</p>
 <p>TE Part # 48131 HYP8 SOLIS 1/0-4/0AWG INDENTER</p>	 <p>TE Part # 600850 ROTO-CRIMP TOOL (ASI)</p>	 <p>TE Part # 48132 HYP8 SOLIS 1/0AWG NEST</p>	

Customers Also Bought

 <p>TE Part #201298-1 FEMALE BLOCK 14 PL.</p>	 <p>TE Part #36921 TERMINAL,SOLIS R 2/0 1/4</p>	 <p>TE Part #36925 TERMINAL,SOLIS R 2/0 1/2</p>	 <p>TE Part #170721-2 SOLISTRAND RINGTONG</p>
 <p>TE Part #DT06-3S-E005 PLG, 3P, BLK, N, CAP</p>	 <p>TE Part #YDTS26F11-98PNV001 PLUG ASSY</p>	 <p>TE Part #284303-000 B-020-22-N</p>	 <p>TE Part #740072-000 SO63-3-01</p>
 <p>TE Part #160001 TERM,SOLIS R 2/0 M10</p>			



Documents

Product Drawings

STRATOTHERM,1/0,5/16,NIPL,45

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_696735-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_696735-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_696735-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.