

1-1903127-3 ✓ ACTIVE

Dynamic Series | Dynamic 1000 Series

TE Internal #: 1-1903127-3

Housing, Housing for Male Terminals, Wire-to-Wire, 26 Position, 2 mm [.079 in] Centerline, Crimp, 2 Row, Black, Mating Retention, Dynamic 1000 Series

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >

DYNAMIC 1100 REC AND TAB HSG



Connector Product Type: **Housing**

Connector & Housing Type: **Housing for Male Terminals**

Connector System: **Wire-to-Wire**

Number of Positions: **26**

Centerline (Pitch): **2 mm [.079 in]**

[All DYNAMIC 1100 REC AND TAB HSG \(53\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	26
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Termination Features

Termination Method to Wire & Cable

Crimp

Mechanical Attachment

Mating Retention

With

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)

2 mm [.079 in]

Dimensions

Row-to-Row Spacing

3.3 mm [.129 in]

Usage Conditions

Operating Temperature Range

-55 – 105 °C [-67 – 221 °F]

Operation/Application

Circuit Application

Signal

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024
(241)Candidate List Declared Against: JUNE
2024 (241)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1827863-3
**DYNAMIC 1100D REC HSG X 26P
 BLACK**


Also in the Series | **Dynamic 1000 Series**



Connector Contacts(40)




Connector Hardware(3)




Insertion & Extraction Tools(2)




PCB Headers & Receptacles(173)



Rectangular Connector Housings(2)



Standard Rectangular Connectors(4)



Wire-to-Board Connector Assemblies
 & Housings(159)

Customers Also Bought



TE Part #1318112-1
DYNAMIC D-2 TAB CONT S L/P



TE Part #1-1827863-1
**DYNAMIC 1100D REC HSG 22P X
 BLACK**



TE Part #1-1747276-4
DYNAMIC D4200 REC HSG 4P/X



TE Part #1-1729372-0
ANVIL



Documents

Product Drawings

DYNAMIC 1100D TAB HSG 26P F/H

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1903127-3_D_c-1-1903127-3-d.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1903127-3_D_c-1-1903127-3-d.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1903127-3_D_c-1-1903127-3-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Agency Approvals

TUV Certificate

English