



Sensors > Pressure Sensors > Media Isolated Pressure Sensors



Pressure: [30 psi]

Pressure Sensor Type: mV Output Pressure Sensors

Pressure Type: Absolute

Output Signal Type: 100mV

Operating Temperature Range: -40 – 125 °C [-40 – 257 °F]

Features

Product Type Features

Pressure Sensor Type	mV Output Pressure Sensors
Pressure Type	Absolute
Sensor Package	O-Ring Mount

Configuration Features

Electrical Connection	Ribbon Cable
-----------------------	--------------

Electrical Characteristics

Supply Current	1.5 mA
----------------	--------

Dimensions

Product Diameter	15.82 mm[.622 in]
Product Height	11.4 mm[.448 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Proof Pressure Range	3X
	30 psi
Output Signal Type	100mV

Other

--	--



Non-Linearity ±	.1 %
Sensor Options	No Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (1% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 86-030G-R
30 PSIG RIBBON CABLE MV PRESSURE SENSOR



TE Part # 86-030A-C
30 PSIA CABLE CONN MV PRESSURE SENSOR



Also in the Series

MEAS 86 Series

Media Isolated Pressure Sensors(40)

Customers Also Bought

TE Part #86-005G-C
5 PSIG MV PRESSURE SENSOR

TE Part #86-300A-C
300 PSIA CABLE CONN MV PRESSURE SENSOR

TE Part #86-100A-C
100 PSIA CABLE CONN MV PRESSURE SENSOR

TE Part #86-015G-C
15 PSIG MV PRESSURE SENSOR

TE Part #86-300G-C
300 PSIG CABLE CONN MV PRESSURE SENSOR

TE Part #9-226176-2
BRAID PIC TERMINAL, LF PLTG

TE Part #20018122-01
830M1-1000 Triaxial 1Kg Tray 25pcs

TE Part #20007013-00
4610-002-120-D

TE Part #20007019-00
4610-100-120-D

TE Part #M3031-000005-01KPG
PRESS XDCR M3031-000005-01KPG

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_86-030A-R_G1.2d_dxf.zip
- English
- Customer View Model



[ENG_CVM_CVM_86-030A-R_G1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_86-030A-R_G1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[86C](#)

English