




Positive Lock | Positive Lock 187

TE Internal #: 928083-1

Receptacle, Receptacle, 1 Position, Straight, Natural, Nylon, Mating Alignment, Cable Mount (Free-Hanging), Positive Lock 187, Crimp Terminal Housings

[View on TE.com >](#)

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
Primary Product Color: **Natural**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Housing Material	Nylon
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 171810-2
POSITIVE LOCK HOUSING RECEPTACLE



TE Part # 1-154719-0
PL 250 REC HSG 1P NYLON NAT



TE Part # 172320-1
POSITIVE LOCK 250 (6.3 MM) HOUSING



TE Part # 520961-1
PL 250 HOUSING BLACK NYLON



TE Part # 177627-1
PL .250 (6.3 MM) HOUSING
RECEPTACLE

TE Part # 343526-1
POSI-LOCK RECPT INSULATOR

TE Part # 1-154719-1
PL 250 REC HSG 1P NYLON NAT

TE Part # 1969630-2
250 HSG POSI-LOK MKI, NAT

TE Part # 1969735-1
POSITIVE LOCK 2P HSG

Also in the Series | Positive Lock 187

Crimp Terminal Housings(86)

Insertion & Extraction Tools(2)

Insulation Boots & Sleeves(7)

Quick Disconnects(57)

Customers Also Bought

TE Part #1577625-1
TERMINAL RT PIDG PEEK STRATO 20
AWG

TE Part #1577646-1
TERMINAL RT PIDG PEEK STRATO 10
AWG

TE Part #ZPF000000000018400
FDBA 50-20-41 PN-K-A5610


TE Part #620069N005
D-108-11CS2883

TE Part #ZPF000000000000289
006-0910-10

TE Part #829470-1
37P ABDECKAPP-SATZ

TE Part #A32355-000
CM-SCE-TP-1/4-4H-4CS34034

TE Part #620068N005
D-108-10CS2883



Documents

Product Drawings

PL 187 REC HSG 1P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_928083-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_928083-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_928083-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.