




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
Mating Tab Width: **4.75 mm** [.187 in]
Mating Tab Thickness: **.51 mm** [.02 in]
PCB Hole Diameter: **4.34 mm** [.171 in]
Profile Height from PCB: **5.85 mm** [.23 in]

Features

Product Type Features

Terminal Features	Stud Hole
-------------------	-----------

Contact Features

Terminal Plating Finish	Matte
PCB Contact Termination Area Plating Material Thickness	1.01 µm[40 µin]
Contact Mating Area Plating Material Thickness	1.01 µm[40 µin]
PCB Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Contact Underplating Material	None
Terminal Size	4.75
Terminal Orientation	45 Bend

Termination Features

Termination Method to PCB	Through Hole - Screw
---------------------------	----------------------



Product Terminates To

Printed Circuit Board

Dimensions

Stud Diameter	4.34 mm[.171 in]
PCB Hole Diameter	4.34 mm[.171 in]
Profile Height from PCB	5.85 mm[.23 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 60920-5
187 FASTON TAB TPBR

TE Part # 60920-1
187 FASTON TAB BR

Also in the Series | FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(42)

Quick Disconnects(208)

Splices(1)

Customers Also Bought

TE Part #5499206-8
A/L UNIV HDR 34P VERT LG LAT

TE Part #2-1761603-1
IDC LOW PRO HDR 6P VERT BLUE

TE Part #5-534206-8
16 MODII VRT DR CE 100/115

TE Part #1577619-1
TERMINAL RT PIDG PEEK STRATO 24-22 AWG



TE Part #170001-3
187 FASTON,TAB,TPBR

TE Part #5-104071-5
25 SYSTEM 50 HDR SRST SHRD SN

TE Part #9-1617515-1
3SBH1195A2=M39016/53-006L

TE Part #20003318-00
PRESS XDCR M32JM-00000E-010BG

TE Part #42214-1
250 FASTON TAB BR

TE Part #1-1617754-7
FCA-410-1620M=M83536/16-020M

Documents

Product Drawings

187 FASTON TAB TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61664-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_61664-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61664-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Application Specification

English