




MAG-MATE

TE Internal #: 63585-1
Tab, Mating Tab Width 4.75 mm [.187 in], Size 2, .36 – .57 mm
Magnet Wire, 27 – 23 AWG Magnet Wire, MAG-MATE, Magnet
Wire Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **4.75 mm** [.187 in]
Mating Tab Thickness: **.51 mm** [.02 in]
Compatible With Cavity Size: **Size 2**
Magnet Wire Size: **27 – 23 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Body Features

Compatible With Cavity Size	Size 2
-----------------------------	--------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Hole
-----------------------	------



Dimensions

Terminal Height	7.63 mm[.3 in]
Magnet Wire Size	.36 – .57 mm
Stock Thickness (Magnet Wire Side)	.41 mm[.016 in]
Product Length	16.76 mm[.66 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Identification Marking

Identification Number	10
-----------------------	----

Packaging Features

Packaging Quantity	12000
Packaging Method	Reel, Reel/Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63486-1 MAG-MATE 110 FAST TAB 020 TPBR	 TE Part # 63664-2 MAG-MATE 27-23 187 FTAB TPBR	 TE Part # 6-316300-7 STD MAG-MATE POKE-IN WITH .187	 TE Part # 63256-2 MAG-MATE 187 FAST TAB
 TE Part # 63273-1 MAG-MATE 187 FAST TAB 020TPBR	 TE Part # 63063-2 TAB, MAG-MATE POKEIN 110F TPBR	 TE Part # 62514-1 MAG-MATE 27-23 187 F TAB TPBR	 TE Part # 316300-4 STD MAG-MATE .187 POKE-IN TAB
 TE Part # 63664-1 MAG-MATE 27-23 187 FTAB TPBR	 TE Part # 62511-1 MAG-MATE 22-20 187 F TAB TPBR	 TE Part # 62514-2 MAG-MATE 27-23 187 F TAB TPBR	 TE Part # 63063-1 MAG-MATE POKE-IN 110F TAB TPBR
 TE Part # 63669-1 MAG-MATE 187 F-TAB TPBR	 TE Part # 63746-1 MAG-MATE 110 F TAB 27-23 TPBR	 TE Part # 63973-1 MAG-MATE 118 TAB TPBR	 TE Part # 63827-1 TERMINAL, MAG-MATE F-TAB TPBR



TE Part # 2825386-1
MAG-MATE 22-20 187 FTAB TPBR

TE Part # 62511-2
MAG-MATE 22-20 187 F TAB TPBR

TE Part # 63107-1
MAG-MATE 187 F TAB 27-23 TPBR

TE Part # 63256-1
MAG-MATE 187 FAST TAB 0198TPBR

Also in the Series

MAG-MATE

Insertion & Extraction Tools(6)

Magnet Wire Terminals(337)

PCB Terminals(1)

Customers Also Bought

TE Part #1971777-3
PTL TPA HIGH TEMP 1 x 3 BLACK

TE Part #5-2232263-3
PTL 1X3 CAP PANEL MT GLW WIRE
KEY A DGR

TE Part #62303-2
AMVAR SPLC 400-1500 016TPBR

TE Part #62305-2
AMVAR SPLC 600-3000 016TPBR

TE Part #42800-2
187 FASTON REC 20-16 AWG TPBR

TE Part #1-2232263-3
PTL 1X4 CAP PANEL MT HOT WIRE
KEYA BLK

TE Part #2238069-1
TERM,SPL,TRI-SLOT,MAG-MATE

Documents

Product Drawings

MAG-MATE 27-23 187 F TAB TPBR

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_63585-1_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63585-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63585-1_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English