


DIMENSIONS



(mm)	Nominal:	Tol. min.:	Tol. max.:
A	40.64	-0.51	0.51
B	4.45	-0.25	0.25
C	10.7	-0.25	0.25
Eff. Parameters			
Ae mm²	Amin mm²	le mm	Ve mm³
99.5	95.1	43.8	4360

INDUCTANCE

AL value (nH)	Test conditions
Nom: 10701 Min.: 8026	10 kHz, < 0.5 mT, 25 °C

LOSS FACTOR

$\tan \delta/\mu$ ($\times 10^{-6}$)	Test conditions
< 20	100 kHz, < 0.25 mT, 25 °C

MARKING

No marking

NOTE

Spec. modifications	Prevoious	Revised