



MEAS EB

TE Internal #: EB1UM-00000P-05KPA
TE Internal Description: PRESS XDCR EB1UM-00000P-05KPA
Miniature Absolute Pressure Transducer
[View on TE.com >](#)



All Miniature Absolute Pressure Transducer (1)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (.15% in component)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-PTT0064
0.1% Wireless Pressure Transducer



TE Part # EP125-7KBS-C00001
P125-A1-7KBG-/L10M

Also in the Series | MEAS EB



Pressure Transducers(1)


Customers Also Bought



TE Part #5749721-7
68 50SR VERT RCPT ASSY



TE Part #541283-000
82A0111-4-9
Single Wall



TE Part #282087-1
AMP SUPERSEAL 1.5 SERIES 3P PL



TE Part #20006465-00
PRESS XDCR M32JM-000105-100PG



TE Part #50832-1
TERMINAL,PIDG PTFE R 22-20 10



TE Part #5104338-9
A/L LOW PRO HDR 50P VERT HT



TE Part #2301840-1
AMPL REC HD20, VERT, 15P, B/L,4-40
S/LOC



TE Part #2-2176347-8
CRGCQ 2010 1K8 1%



TE Part #282049-023
44A0111-24-9



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_EB1UM-00000P-05KPA_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_EB1UM-00000P-05KPA_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_EB1UM-00000P-05KPA_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

EB100

English