




TE Internal #: TAD14141311-001
M12 Pigtail Cable Assembly, 4 Position, .5 m, Industrial Ethernet,
SERCOS III, Code D, M12 Plug, Shielded, Single Ended,
PA66+25GF
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > Ethernet, Sercos-III M12-D 4pos PVC Red



M8/M12 Application Type: **Industrial Ethernet**
Industrial Protocols: **SERCOS III**
Number of Positions: **4**
Connector & Keying Code: **D**
Cable Assembly Type: **M12 Pigtail**

[All Ethernet, Sercos-III M12-D 4pos PVC Red \(18\)](#)

Features

Product Type Features

Cable Assembly Type	M12 Pigtail
Cable Assembly (End A)	M12 Plug

Configuration Features

Number of Strands	7
Number of Positions	4

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Cable Color	Red
Connector Color (End A)	Black
Jacket Material	PVC
Wire Color (Base)	Yellow-Orange-White-Blue
Conductor Material	Tinned Copper



Connector & Keying Code	D
Contact Features	
Contact Current Rating (Max)	4 A
Mechanical Attachment	
Connector Orientation (End A)	Straight
Housing Features	
Housing Material	PA66+25GF
Dimensions	
Outside Cable Diameter	6.5 mm
Wire Size	22 AWG
Operation/Application	
M8/M12 Application Type	Industrial Ethernet
Shielded	Yes
Industry Standards	
IP Rating	IP67
Industrial Protocols	SERCOS III
Packaging Features	
Packaging Quantity	5
Packaging Method	Bag
Other	
Cable Assembly Length	.5 m
Cable Assembly Configuration	Single Ended
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold:



Pb (1.9% in Component)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T4143512041-000
M12,FRONT MOUNTING,FEMALE,D
CODE,4P

Customers Also Bought




TE Part #1411001-1
SEALED HARN ASSY W/O CPA KEY B



TE Part #2333393-3
QSFP 25GIG 30AWG 1 METER



TE Part #4-1630012-2
HSC150 50R 5%



TE Part #T4161410005-002
RPC-M12-FR-5CON-PVC-1.0SH



TE Part #102387-4
20 MODIV HSG COMP DR .100 POL

TE Part #1825851-1
AMPMODU MOD IV LATCH for
AMPLA

TE Part #4-1971798-1
NEW GI CONN2.5 HDR ASMBLY 4P
NC D1.0

TE Part #5745583-1
UNIV SLIDLTCH KIT SZ 2

TE Part #2208338-1
6POS,NANOMQS,REC HSG,CODA

TE Part #4-2170705-2
CAGE ASSY, QSFP28 1X1, SPRING,
HS, LP

Documents

Product Drawings

M12D4-MS-PVC TYPE B RED-0.5M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_TAD14141311-001_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_TAD14141311-001_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_TAD14141311-001_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8/M12 Cable Assemblies Brochure

English

Product Specifications

Application Specification

English



Agency Approvals

UL

English