


12	11	10	9	8	7	6	5	4	3	2	1
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"		
192030156	C-T-328-08	192030098	C-T-328-08T	8	.173 [4.39]	.375 [9.53]	.303 [7.70]	.785 [19.94]	1.234 [31.34]		
192030099	C-T-328-10	192030100	C-T-328-10T	10	.198 [5.03]						
192030182	C-T-330-14	192030101	C-T-330-14T	14	.265 [6.73]	.530 [13.46]	.393 [9.98]	.952 [24.18]	1.234 [31.34]		



PARTS ON TAPE

- NOTES:
- MATERIAL: COPPER (STOCK THICKNESS .040±.001 [1.02])
PLATING: WATTS BATH NICKLE (.0002 MIN)
 - BRAZED SEAM
 - WIRE SIZE: 12 - 10 AWG
4.0 - 6.0 MM²
 - MAX. OPERATING TEMP : 650 °F
343 °C
 - "UL" LISTING #E32244
"CSA" LISTING #18689
 - ALL DIMENSIONS IN INCHES/[MM].
 - PARTS ARE ROHS COMPLIANT.
 - DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS	P1	RELEASE DATE	2024/05/13	16:21:59
-----------------	----	--------------	------------	----------

12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	---	---	---	---	---	---	---	---	---