




Terminals & Splices > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **1.8 mm [.071 in]**

Mating Tab Thickness: **.64 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **20 – 16 AWG**

[All MULTILOCK, RECEPTACLE AND TAB \(111\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	1.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Gold
Typical Current Rating	10 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1.8 mm[.071 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Gold (Au)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire



Dimensions

Compatible Insulation Diameter Range	2 – 2.6 mm[.079 – .102 in]
Wire Size	.5 – 1.25 mm²
Wire Size Search	16 AWG, 17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C[176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-M9194-CH8172 MULTILOCK, CONNECTOR HOUSING	 TE Part # 91573-1 CCII 070 SERIES REC TAB 20-16 ASSY	 TE Part # 755430-2 EXT, TOOL ASSY	 TE Part # 348793-4 SHORTING CONN RECPT HSG. (BRIG
 TE Part # 58521-2 PRO-CRIMPER DIE	 TE Part # 2151168-1 OCEAN_2.0_Applicator-S-090F102F-RSM	 TE Part # 2151168-2 OCEAN_2.0_Applicator-S-090F102F-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp
 TE Part # 5-2151168-1 OCEAN_2.0_Applicator-S-090F102F-RSM	 TE Part # 5-2151168-2 OCEAN_2.0_Applicator-S-090F102F-RSA	 TE Part # 7-2151168-7 OCEAN_2.0_SPARE_PART_KIT-090F102F	 TE Part # 174926-5 070 MLC W-W PLUG HSG 13P BLUE
 TE Part # 174927-4 070 MLC W-W PLUG HSG 15P GREEN	 TE Part # 173852-5 070 MULTILOCK PLUG 14P BLUE	 TE Part # 174923-5 070 MLC W-W PLUG HSG 6P BLUE	 TE Part # 175567-6 HYBRID I/O PLUG HSG 26P GRAY



TE Part # 917635-1
040/070 HYBRID 12POS PLUG HSG

TE Part # 172902-2
SCCS 14P PLUG HSG

TE Part # 173850-4
070 MLC PLUG HSG 8P GREEN

TE Part # 173853-7
070 MLC PLUG HSG 18P YELLOW

Also in the Series | Multilock Connector System

Automotive Connector Caps & Covers
(10)

Automotive Connector Locks & Position Assurance(3)

Automotive Housings(445)

Automotive Terminals(117)

Connector Seals & Cavity Plugs(2)

Insertion & Extraction Tools(6)

Other Automotive Connector Accessories(12)

PCB Headers & Receptacles(134)

Customers Also Bought

TE Part #174967-2
MULTILOCK, CONNECTOR HOUSING

TE Part #2317657-1
AV25 SPM 3A MOVING RING R&G 12V FL

TE Part #DTM04-2P-P007
DEUTSCH DTM Housings

TE Part #776535-1
AS16,CAP ASSY,ST,03P,E SEAL,CODE A

TE Part #173716-2
MULTILOCK, RECEPTACLE AND TAB

TE Part #174931-1
070 MLC W-W CAP HSG 8P NATURAL



Documents

Product Drawings

070 REC CONTRACT 20-16

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_173631-2_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_173631-2_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_173631-2_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MULTILOCK Connector System

English

Product Specifications

Application Specification

English

.070 Series Receptacle Contact

English

Instruction Sheets

HYBRID I/O CONNECTOR

English

Customer Manual (non U.S.)

English

HYBRID I/O CONNECTOR

English

Customer Manual (non U.S.)

English