

S31B0C-P07LFG0-5000  
series\_b  
type\_s3





General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S31B0C-P07LFG0-5000 |
| Termination       | solder              |
| Size              | 1                   |
| Locking principle | push                |
| Coding            | 0_key               |
| Cable Diameter    | cable_mini_50       |
| Cable outlet      | standard            |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.



The pin layout corresponds to the view on the termination area

Contact insert description

|                      |         |
|----------------------|---------|
| Number of contacts   | 7       |
| Contact type         | sockets |
| Contact diameter     | 07mm    |
| Insulator material   | peek    |
| Wire cross section   | 22_awg  |
| Termination          | solder  |
| Termination diameter | 085mm   |

reverse\_gender\_on\_request

Technical information

|                                          |         |               |
|------------------------------------------|---------|---------------|
| Max. creepage and air clearance distance | 07_mm   | 10_mm         |
| Nominal current single contact           | 075_a   | iec_60512_5_2 |
| Nominal current insert                   | 4,875 A | vde_0298_4    |
| Test voltage                             | 1_kv_ac | sae_13441     |

safety\_text

**Mechanical and environmental data**

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip68     |
| Operating temperature | 40_120_c |
| Mating cycles         | 5000     |

mated

**Material and surface treatments**

|         |               |
|---------|---------------|
| Housing | m_chrome      |
| Contact | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text