




TERMI-FOIL

TE Internal #: 51943
End Tap, Type 13, Mating Tab Width 6.35 mm [.25 in], Tin Plating,
Box, 150 °C [302 °F], TERMI-FOIL, Foil Terminals
[View on TE.com >](#)

Terminals & Splices > Foil Terminals



Foil Terminal Type: **End Tap**
Foil Terminal Body Type: **Type 13**
Mating Tab Width: **6.35 mm [.25 in]**
Accepts Foil Thickness (Max): **.76 mm [.03 in]**
Terminal Plating Material: **Tin**

Features

Body Features

Foil Terminal Body Type	Type 13
-------------------------	---------

Contact Features

Foil Terminal Type	End Tap
Mating Tab Width	6.35 mm[.25 in]
Terminal Plating Material	Tin

Termination Features

Accepts Foil Thickness (Max)	.76 mm[.03 in]
------------------------------	----------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	150 °C[302 °F]

Packaging Features

Packaging Quantity	100
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [TERMI-FOIL](#)



Customers Also Bought



TE Part #3-644456-2
02P MTA100 HDR ASSY (NARROW)




TE Part #2-2176231-9
3522 150R 1% 3W



TE Part #1676480-1
CRG0402 1% 100K



TE Part #737015-3
PL TERMINAL RECEPTACLE 4-6 MM2 PTPBR



TE Part #52195
TERMINAL,TERMI-FOIL 16-14



TE Part #1676480-2
CRG0402 1% 100R



TE Part #2238178-1
187 X 020 POS LOC REC 20-16 NISTL



TE Part #8B-0011-001-000
623/923 PROTECTION CAP



TE Part #8B-0013-001-000
623 PROTECTION CAP

Documents

- Product Drawings

TAB, TERMI-FOIL END TAP TERMINAL

English
- CAD Files

3D PDF

3D
- Customer View Model

ENG_CVM_CVM_51943_G.2d_dxf.zip

English

Customer View Model

[ENG_CVM_CVM_51943_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_51943_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[PRE-SET HAND TOOL,TERMI-FOIL](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese