




Connectors > PCB Connectors > PCB Headers & Receptacles > High Pin Count Header



Connector System: Wire-to-Board

Number of Positions: 135

Centerline (Pitch): 2.2 mm, 2.5 mm, 3.2 mm [.087 in, .098 in, .125 in]

Sealable: No

PCB Mount Orientation: Right Angle

[All High Pin Count Header \(65\)](#)

Features

Product Type Features

Mixed & Hybrid Header	Yes
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	4
Number of Positions	135
PCB Mount Orientation	Right Angle
Number of Rows	7

Electrical Characteristics

Voltage Rating (Max)	12 VDC
----------------------	--------



Nominal Voltage Architecture	12 V
Operating Voltage	12 VDC

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Type	Tab
Contact Mating Area Plating Material	Gold (Au), Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mounting Holes	With
Mating Alignment	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.2 mm, 2.5 mm, 3.2 mm[.087 in][.098 in][.125 in]
--------------------	---

Dimensions

Connector Length	19.5 mm[.767 in]
Connector Width	112.7 mm[4.437 in]
	.063 in

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	4
--------------------	---



Packaging Method	Tube
Other	
Interface Number	1123325, 1123326, 1123328, 1123329

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | 0.64/025 Connector System



Automotive Connector Caps & Covers (5)



Automotive Connector Locks & Position Assurance(1)



Automotive Housings(127)




Automotive Terminals(16)



Connector Seals & Cavity Plugs(1)




Other Automotive Connector Accessories(4)



PCB Headers & Receptacles(158)


Customers Also Bought



TE Part #1318384-2
025 I/O CAP HSG ASSY 40P




TE Part #5787962-1
.8MM CHAMP STACK RCPT ASSY




TE Part #5055323-9
06 POWER TAP ASSY .125



TE Part #1062-12-0222
SOC, SF, SIZE 12, 10, NI/NI




TE Part #1734517-1
STD USB TYPE B, VERTICAL, SMT, GRD FINGER



TE Part #770678-1
SEAL PLUG, AMPSEAL



TE Part #964972-1
EINZELLEITERDICHTNG



TE Part #6437288-2
SUPER SEAL 34POS CAP ASSY



TE Part #2013978-1
Mini HDMI, RA, SMT



TE Part #1-5175975-2
040 MLC MK2 20POS CAP ASSY H AU

Documents



Product Drawings

0.64/1.0 135POS CAP ASSY

Japanese

0.64/1.0 135POS CAP ASSY

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6376430-2_AC.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6376430-2_AC.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6376430-2_AC.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Crimping .040III Unsealed Contact, Receptacle

Japanese

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

025/040 I/O Connector

Japanese

Instruction Sheet (non U.S.)

Japanese

025/040 I/O Connector

Japanese