




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **5.21 mm [.205 in]**

Terminal Orientation: **Straight**

Features

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	5.21 mm[.205 in]
Terminal Orientation	Straight
Contact Base Material	Steel
Terminal Plating Material	Nickel
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Compatible Insulation Diameter Range	2.54 – 3.81 mm[.1 – .15 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Packaging Features

Packaging Quantity	16000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2150084-1
OCEAN_2.0_APPLICATOR-E-100F180F-REM



TE Part # 2150084-2
OCEAN_2.0_APPLICATOR-E-100F180F-REA



KIT
TE Part # 7-2150084-7
OCEAN_2.0_SPARE_PART_KIT-100F180F

Also in the Series | FASTON 205



Crimp Terminal Housings(3)



PCB Terminals(10)



Quick Disconnects(35)

Customers Also Bought



TE Part #521367-1
ULTRA-POD 250 ASSY REC 18-14 AWG BR



TE Part #63933-1
PL .250 TERMINAL REC 22-18 AWG BR



TE Part #1742899-1
187 FASTON,REC.,18-16 OR 2X18 AWG,NPST



TE Part #521411-1
ULTRA-POD 250 ASY REC 22-18 AWG BR




TE Part #42660-1
250 FASTON REC 18-14 AWG BR



TE Part #1742883-1
187 FASTON,REC.,20-16 AWG,NPST



TE Part #7-1241961-2
STD TIM HOUSING MKII 2POS



TE Part #2-176498-6
187 HSG. PL MKII REC. 15mm 2P BLUE



TE Part #5-1969536-4
HSG,RECP,POSILOK MKIII ,250SER,3P, 2CIR



TE Part #1-176282-5
AMP UNIVERSAL POWER CAP 2P GREEN



Documents

Product Drawings

205 FASTON,REC.,18-14 AWG,NPST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1742594-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1742594-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1742594-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English