



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **9**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacked Levels	Without
Wire Entry Location	Side
Number of Positions	9
Number of Rows	1
Wire Entry Angle	90°

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
-----------------------	-------



Product Orientation	Vertical
Contact Features	
Contact Mating Area Plating Material	Tin
Contact Base Material	Brass
Contact Current Rating (Max)	17.5 A
Termination Features	
Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3
Connector Mounting Type	Board Mount
Housing Features	
Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]
Dimensions	
Wire Size	.05 – 3 mm²
Usage Conditions	
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
Operation/Application	
Circuit Application	Power & Signal
Packaging Features	
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUNE 2024 (241)
SVHC > Threshold:
Pb (.77% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 796949-9
9 POS TERMI-BLOK PCB MOUNT



TE Part # 1-796949-8
18POS TERMI-BLOK PCB MOUNT




TE Part # 1-796949-9
19POS TERMI-BLOK PCB MOUNT



TE Part # 796683-9
TERMI-BLOK PCB MOUNT 90 9P.


Customers Also Bought




TE Part #282841-5
TERMI-BLOK PCB MOUNT 5P. 5



TE Part #1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Part #282841-6
TERMI-BLOK PCB MOUNT 6P. 5



TE Part #1-282841-2
TERMI-BLOK PCB MOUNT 12P.5



TE Part #282841-7

[TERMI-BLOK PCB MOUNT 7P. 5](#)

TE Part #7-2176092-0

[RP 2A 0.25W 4K02 0.1% 25PPM 1K RL](#)

TE Part #7-1625867-0

[RP 1J 0.166W 33R2 0.1% 25PPM 1K RL](#)

TE Part #4-2176366-5

[RQ 0603 1K24 0.1% 10PPM 1K RL](#)

TE Part #7-2176365-7

[RQ 0603 249R 0.1% 10PPM 1K RL](#)

Documents

Product Drawings

[TERMI-BLOK PCB MOUNT 9P. 5](#)

English

CAD Files

Customer View Model

[ENG_CVM_282841-9_H4.3d_igs.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_282841-9_H4.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_282841-9_H4.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_282841-9_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_282841-9_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_282841-9_C.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English