



Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Mounting**

Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Ivory**

Primary Product Material: **PA 66**

Number of Positions: **18**

Features

Product Type Features

Hardware Accessory Function	Mounting
Connector Hardware Accessory Type	Holder

Configuration Features

Number of Positions	18
---------------------	----

Body Features

Primary Product Color	Ivory
Primary Product Material	PA 66

Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Dimensions

Product Width	8.5 mm[.334 in]
Product Length	22.3 mm[.878 in]
Product Height	6.9 mm[.271 in]
Row-to-Row Spacing	6.5 mm
Wire Size	30 – 22 AWG



Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-3980700-DRWBSV
CT 2mm Dbl Row Assembly w/Boss:
Vert.

TE Part # CAT-AM7017-H8172
AMP COMMON TERMINATION
HOUSINGS

TE Part # 1-292138-8
CT DOUBLE ROW ASSY H 18P HDR N

Also in the Series

AMP CT

Connector Contacts(8)

Connector Hardware(46)

PCB Headers & Receptacles(756)

Wire-to-Board Connector Assemblies
& Housings(255)

Customers Also Bought

TE Part #326861
PIDG SPD 22-16 COMM 22-18MIL 6

TE Part #173977-9
AMP COMMON TERMINATION
HOUSINGS

TE Part #292132-4
CT P/HDR BOX V 4P NAT

TE Part #1-292138-8
CT DOUBLE ROW ASSY H 18P HDR N

TE Part #350689-3
UMNL SOK 24-18 PTPPHBZ L/P

TE Part #1658622-2
14 NOVO MIL/CTR 30DP,LEAD FREE

TE Part #4-640426-2
12P MTA156 CONN ASSY 18AWG
ORA

TE Part #3-640426-5
05P MTA156 CONN ASSY 18AWG
ORA

TE Part #641324-2
RECEPT PIDG FASTON 26-24 110



Documents

Product Drawings

CT DBL ROW HOLDER,MT,18P,NA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-179608-8_A4.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-179608-8_A4.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-179608-8_A4.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Crimping AMP 2.0mm Pitch CT Receptacle Contact

English

Agency Approvals

CSA Certificate

English