



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**
Connector & Housing Type: **Tab Housing**
Number of Positions: **1**
Terminal Orientation: **Straight**
Primary Product Color: **Natural**

Features

Product Type Features

| | |
|-----------------------------------|--------------|
| Sealable | No |
| Connector & Contact Terminates To | Wire & Cable |
| Connector & Housing Type | Tab Housing |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 1 |
|---------------------|---|

Body Features

| | |
|-----------------------|---------|
| Primary Product Color | Natural |
|-----------------------|---------|

Contact Features

| | |
|--------------------------|----------|
| Terminal Type | Tab |
| Terminal Orientation | Straight |
| Contact Mating Retention | Without |

Mechanical Attachment

| | |
|-----------------------|---------|
| Mating Alignment Type | None |
| Mating Alignment | Without |



| | |
|-------------------------|----------------------------|
| Connector Mounting Type | Cable Mount (Free-Hanging) |
|-------------------------|----------------------------|

Housing Features

| | |
|------------------|--------------|
| Housing Material | Polyethylene |
|------------------|--------------|

Dimensions

| | |
|----------------|-----------------|
| Product Length | 24.1 mm[.95 in] |
|----------------|-----------------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 5000 |
|--------------------|------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 360041-1
187 FASTON HSG.,TAB,1 POS,
NATRUAL

TE Part # 881339-2
SLEEVE FOR .250 SRS FASTON TAB

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(426)

Splices(4)

Customers Also Bought

TE Part #172337-1
MINI UMNL PLUG HOUSING 3P

TE Part #170891-2
250 FASTON HSG.,FLAG,REC.,
NATRUAL

TE Part #60701-1
FF 250 TAB 14-10AWG TPBR

TE Part #2364568-1
AVH19 FLT SS MT NO LED 16A

TE Part #965601-2
8POS MQS REC COD II

TE Part #167296-1
50P.HDP20 PLUG ASSY

TE Part #735075
250 FASTON HSG. REC. 1P CLEAR

TE Part #1-965600-1
MQS KAPPE 8P



Documents

Product Drawings

250 FASTON HSG. REC. 1P NATURAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_735093_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_735093_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_735093_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

6,35 FASTON RECPTACLES AND TAB SLEEVES

English

Product Specification

English