



Sensors > Pressure Sensors > Pressure Transducers > Compact Industrial Pressure Transducer



Pressure Sensor Type: Industrial Pressure Transducer

Pressure: 10 bar [ 145.03 psi ]

Pressure Type: Gauge

Supply Voltage Range: 2.7 – 5 V

Output Signal Type: 14 bit ADC

[All Compact Industrial Pressure Transducer \(41\)](#)

Features

Product Type Features

Pressure Sensor Type	Industrial Pressure Transducer
Pressure Type	Gauge

Configuration Features

Electrical Connection	Cable 1 m
-----------------------	-----------

Electrical Characteristics

Supply Voltage Range	2.7 – 5 V
----------------------	-----------

Dimensions

Hex Width Across Flats	22.2 mm[.875 in]
Product Height	56.64 mm[2.23 in]

Usage Conditions

Pressure	10 bar[145.03 psi]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Output Signal Type	14 bit ADC
Proof Pressure Range	2X Rated
Pressure Accuracy	±0.25% FSO



Other

Sensor Options	Adhesive Label, No Snubber
Port Fitting	1/4-19 BSPT

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Decamethylcyclopentasiloxane (D5) (.12% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.26% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-PTT0068  
Compact Industrial Pressure Transducer

Also in the Series | MEAS M3200



Pressure Transducers(41)

Customers Also Bought



TE Part #5499206-8  
A/L UNIV HDR 34P VERT LG LAT



TE Part #2-5747708-0  
25 RCPT SP/FMS BRDLK



TE Part #5-534206-8  
16 MODII VRT DR CE 100/115




TE Part #640584-1  
08P UMNL HDR ASSY R/A 94VO




TE Part #2-1445057-3  
MICRO MNL HDR ASSY SINGLE ROW



TE Part #5-104071-5  
25 SYSTEM 50 HDR SRST SHRD SN




TE Part #6-1879627-1  
H4P 3K3 1% 100PPM



TE Part #776087-1  
23POS,PIN DIA 1.3,HDR ASSY,90DEG, COD 1



TE Part #9-1617515-1  
3SBH1195A2=M39016/53-006L



TE Part #1-1617754-7  
FCA-410-1620M=M83536/16-020M



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_20003318-00\_H.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_20003318-00\_H.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_20003318-00\_H.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M3200 Pressure Transducer

English