




Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Guide Hardware**

Connector Hardware Accessory Type: **Guide Pin Kit**

Primary Product Color: **Natural**

Primary Product Material: **Stainless Steel**

Operating Temperature (Max): **150 °C [302 °F]**

Features

Product Type Features

Hardware Accessory Function	Guide Hardware
Connector Hardware Accessory Type	Guide Pin Kit

Body Features

Primary Product Color	Natural
Primary Product Material	Stainless Steel

Mechanical Attachment

Hardware Type Included	Nuts and Lockwashers
Thread Size	6-32 UNC-2B

Dimensions

Product Width	6.35 mm[.25 in]
Product Length	21.08 mm[.83 in]
Product Height	7.35 mm[.289 in]

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]



Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 201310-3 MALE BLOCK. 75 PL.-MIN. RECT.	 TE Part # 201311-1 FEMALE BLOCK MIN. RECT.	 TE Part # 201345-1 104 PL. MALE BLOCK-PHEN.	 TE Part # 201310-1 MALE BLOCK 75 PL.-MIN RECT.
---	---	--	---





TE Part # 201047-2
SERIES "M" ST. STL. GUIDE SOC.



TE Part # 203966-1
CORNER GUIDE SKT,M SERIES

Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(7)



Connector Caps & Covers(12)



Connector Hardware(18)



Connector Strain Relief(11)



Rack & Panel Connectors(1)




Rectangular Power Connectors(65)

Customers Also Bought



TE Part #201911-1
JACKSCREW KIT



TE Part #201848-5
STRAIN RELIEF CLAMP UNASSEM.



TE Part #1-200874-2
SERIES "M" JACKSCREW STUD ASSY



TE Part #200875-7
SKT ASSY,M SERIES



TE Part #1-200835-1
SERIES'M' MIN. RECT. GUIDE SOC



TE Part #201501-1
SPIROL PIN



TE Part #201368-4
75 PL. EXTERNAL PIN HOOD



TE Part #203744-4
160-POS. PIN HOOD EXTERNAL



Documents

Product Drawings

SERIES "M" MIN RECT GUIDE PIN

English

CAD Files

Customer View Model

ENG_CVM_1-201046-2_U.3d_igs.zip

English

Customer View Model

ENG_CVM_1-201046-2_U.3d_stp.zip

English

Customer View Model

ENG_CVM_1-201046-2_U.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_1-201046-2_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-201046-2_R.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-201046-2_R.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English