








PRODUCT NUMBER
10131868-104LF





SECTION Z - Z



spec ref -				dr	Stalin Alosius	2015/09/23	projection 	mm 	size	A3	scale	2:1	
tolerance std				eng	Stalin Alosius	2016/02/23			ecn no				ELX-I-22463-4
ISO 406 ISO 1101				chr	-	-			rel level				Released
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr	K-Paul Biju	2016/02/24	product family		METRAL HDXS				
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCi	title	POWER OCTIS RA BC WITH COMBO HSG		dwg no	10131868-104		rev B		
		0.XX	±0.10										
		0.XXX	±0.050			2 PWR PIP TERMINATION							
	angular	0°	±2°	cat. no.				-	Product - Customer Drw		sheet 1 of 4		






D



1. MATERIAL :
 - RESIN - LCP, GLASS FILLED, FLAME RETARDANT ACC
 - FLAMMABILITY CLASSIFICATION - UL94-V0
 - SIGNAL & POWER CONTACTS - COPPER ALLOY
2. PLATING :
 - PURE TIN ON POWER CONTACTS
3. PRODUCT SPECIFICATION: GS-12-1334
4. APPLICATION SPECIFICATION: GS-20-0454
5. PACKAGING - TAPE & REEL
PACKAGING SPECIFICATION: GS-XX-XXX
6. UNDER PLATING FOR CONTACTS IS 1.27µm NICKEL.
7. PRODUCT WILL WITHSTAND EXPOSURE TO 260° FOR
60 SECONDS IN A CONVECTION, INFRA RED OR VAPOUR PHASE
REFLOW OVEN
8. PRODUCT WHERE THE PARTNUMBER ENDS IN LF MEETS
EUROPEAN DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-47-0004.

spec ref -				dr	Stalin Alosius	2015/09/23	projection 	mm 	size	A3	scale	2:1	
tolerance std				eng	Stalin Alosius	2016/02/23			ecn no				ELX-I-22463-4
ISO 406 ISO 1101				TOLERANCES UNLESS OTHERWISE SPECIFIED					rel level				Released
				chr	-	-							
				appr	K-Paul Biju	2016/02/24	product family		METRAL HDXS				
surface ISO 1302	linear	0.X	±0.3	Amphenol FCI	title	POWER OCTIS RA BC WITH COMBO HSG 2 PWR PIP TERMINATION			dwg no	10131868-104		rev	B
		0.XX	±0.10										
		0.XXX	±0.050										
	angular	0°	±2°		cat. no.	-	Product - Customer Drw			sheet 2 of 4			

PACKAGING SPECIFICATION



TAPE & REEL PACKING DETAILS





NOTES:


1. CONNECTORS PACKED PER REEL : 150 PIECES
2. PACKAGING DETAILS AS PER EIA-481 STD.
3. PACKING SHOULD BE ANTISTATIC.
4. MATERIAL :
CARRIER TAPE : POLYSTYRENE
COVER TAPE : POLYSTYRENE

spec ref -				dr	Stalin Alosius	2015/09/23	projection 	mm 	size	A3	scale	2:1	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Stalin Alosius	2016/02/23			ecn no	ELX-I-22463-4			
				chr	-	-							
				appr	K-Paul Biju	2016/02/24	product family				--	rel level	
surface ISO 1302	linear	0.X	±0.3	Amphenol FCi	title POWER OCTIS RA BC WITH COMBO HSG 2 PWR PIP TERMINATION				dwg no	10131868-104			rev B
		0.XX	±0.10										
		0.XXX	±0.050		cat. no.					Product - Customer Drw			
	angular	0°	±2°										

BOARD CONNECTOR WITH BULKHEAD

SCALE 2:1



spec ref -				dr	Stalin Alosius	2015/09/23	projection 	mm 	size	A3	scale	1:2
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Stalin Alosius	2016/02/23			ecn no	ELX-I-22463-4		
				chr	-	-						
				appr			K-Paul Biju		2016/02/24	product family		METRAL HDXS
surface ISO 1302	linear	0.X	±0.3	Amphenol FCi	POWER OCTIS RA BC WITH COMBO HSG				dwg no	10131868-104		rev B
		0.XX	±0.10									
		0.XXX	±0.050									
	angular	0°	±2°	cat. no.	-	Product - Customer Drw				sheet 4 of 4		