




Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Coding & Keying**

Connector Hardware Accessory Type: **Keying Plug**

Primary Product Color: **Red**

Primary Product Material: **PA**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Hardware Accessory Function	Coding & Keying
Connector Hardware Accessory Type	Keying Plug

Body Features

Primary Product Color	Red
Primary Product Material	PA

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 926476-3 MOD 4 HSG	 TE Part # 926475-3 03P MODU 4 HSG.S.R.	 TE Part # 926475-4 MOD 4 HSG	 TE Part # 926476-4 2X4P MODU 4 HSG.
 TE Part # 926476-6 MOD 4 HSG	 TE Part # 1-926476-0 MOD 4 HSG	 TE Part # 926475-8 MOD 4 HSG	 TE Part # 1-926475-0 MOD 4 HSG
 TE Part # 1-926476-7 MOD 4 HSG	 TE Part # 926475-7 MOD 4 HSG	 TE Part # 926475-5 MOD 4 HSG	 TE Part # 926476-8 MOD 4 HSG



TE Part # 926475-6
MOD IV HSG SR 6 POS



TE Part # 926476-5
MOD 4 HSG



TE Part # 1-926476-3
MOD 4 HSG



TE Part # 926476-7
MOD 4 HSG



TE Part # 3-926475-0
MOD 4 HSG



TE Part # 926476-9
MOD 4 HSG



TE Part # 1-926475-2
MOD 4 HSG



TE Part # 1-926475-3
MOD 4 HSG

Also in the Series | **Modu Connector System**



Automotive Connector Caps & Covers
(3)




Board-to-Board Jumpers & Shunts(5)



Connector Caps & Covers(1)



Connector Hardware(4)



PCB Headers & Receptacles(1110)

Customers Also Bought



TE Part #8-338069-0
MICRO-MATCH SMD FTE



TE Part #1-770178-0
06P MINI-UMNL ASSY VO SNNI*



TE Part #966870-1
MOD2 ST-WANNE 2X 8P



TE Part #3-1625890-1
2W SM M/OX 5% 220R






TE Part #282901-2
TERMI-BLOK PCB MOUNT 2ND 2P.5,



TE Part #K2001858
Toggle Switch 08-2-1-14 F



TE Part #K1002956
Toggle Switch 08-4-1-13



TE Part #173799-E
IDCCS SMC 1,27 12 * AU AUI 100 PVC

Documents

Product Drawings

MOD2 KODIERSTUECK

English

CAD Files

Customer View Model

ENG_CVM_926498-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_926498-3_1.3d_stp.zip

English

Customer View Model

ENG_CVM_926498-3_1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English