

LIT 2-12 - Surge protection device



2804694

<https://www.phoenixcontact.com/us/products/2804694>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection in one-piece 6.2 mm wide DIN rail module for two floating signal wires. Tested in acc. with the protection types in Ex areas: Ex ia IIC / Ex iaD.

Your advantages

- Space saving with a narrow overall width of just 6 mm
- Install quickly and error-free with DIN rail connectors
- No signal interference with reliable attenuation

Commercial data

Item number	2804694
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL02
Product key	CL2211
Catalog page	Page 92 (C-6-2013)
GTIN	4046356462198
Weight per piece (including packing)	65.94 g
Weight per piece (excluding packing)	55.75 g
Customs tariff number	85363010
Country of origin	DE

LIT 2-12 - Surge protection device

2804694

<https://www.phoenixcontact.com/us/products/2804694>



Technical data

Product properties

Product type	Surge protection for MCR technology
Product family	LINETRAB
IEC test classification	C1
	C2
	C3
	D1
Type	DIN rail module, one-piece

Data management status

Article revision	15
------------------	----

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	12 V DC
-----------------------	---------

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.8 Nm
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 14

Ex data

Maximum inner capacitance C_i	typ. 3 nF
Max. internal inductance L_i	< 1 μ H
Max. input current I_i	500 mA ($T_4 / \leq 80^\circ\text{C}$)
	500 mA ($T_5 / \leq 50^\circ\text{C}$)
	500 mA ($T_6 / \leq 40^\circ\text{C}$)
Max. input voltage U_i	18 V DC
max. input power P_i	635.00 mW
Maximum inner time factor (R_i/L_i)	10 μ s

Dimensions


LIT 2-12 - Surge protection device

2804694

<https://www.phoenixcontact.com/us/products/2804694>



Dimensional drawing



Width	6.2 mm
Height	93.1 mm
Depth	102.5 mm (incl. DIN rail 7.5 mm)

Material specifications

Color	anthracite grey (RAL 7016)
Flammability rating according to UL 94	V-0
Insulating material	PBT
Housing material	PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Maximum continuous voltage U_C	18 V DC 13 V AC
Rated current	500 mA (40 °C)
Operating effective current I_C at U_C	$\leq 2 \mu A$
Residual current I_{PE}	$\leq 2 \mu A$
Nominal discharge current I_n (8/20) μs (line-line)	350 A
Nominal discharge current I_n (8/20) μs (line-ground)	5 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	500 A 1 kA (in total)
Total discharge current I_{total} (8/20) μs	10 kA 20 kA (1x)
Max. discharge current I_{max} (8/20) μs maximum (line-line)	350 A
Max. discharge current I_{max} (8/20) μs maximum (line-earth)	10 kA 20 kA (in total)
Nominal pulse current I_{an} (10/1000) μs (line-line)	70 A
Nominal pulse current I_{an} (10/1000) μs (line-earth)	50 A 100 A (in total)
Output voltage limitation at 1 kV/ μs (line-line) spike	$\leq 50 V$
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 650 V$
Residual voltage at I_n (conductor-conductor)	$\leq 50 V$
Residual voltage with I_{an} (10/1000) μs (line-line)	$\leq 50 V$

LIT 2-12 - Surge protection device

2804694

<https://www.phoenixcontact.com/us/products/2804694>



Voltage protection level U_p (line-line)	≤ 50 V (C1 - 500 V / 250 A)
	≤ 35 V (C3 - 10 A)
	≤ 40 V (C3 - 70 A)
Voltage protection level U_p (line-earth)	≤ 650 V (C1 - 500 V / 250 A)
	≤ 650 V (C2 - 10 kV / 5 kA)
	≤ 650 V (C3 - 10 A)
	≤ 700 V (C3 - 50 A)
	≤ 700 V (D1 - 500 A)
Response time t_A (line-line)	≤ 1 ns
Response time t_A (line-earth)	≤ 100 ns
Input attenuation aE, sym.	typ. 0.3 dB (1.5 MHz/50 Ω)
	typ. 0.3 dB (500 kHz / 150 Ω)
Cut-off frequency f_g (3 dB), sym. in 50 Ω system	typ. 5 MHz
Cut-off frequency f_g (3 dB), sym. in 150 Ω system	typ. 1.7 MHz
Capacity	≤ 1.5 nF (per path)
Resistance per path	0 Ω
Surge protection fault message	none
Max. required back-up fuse	500 mA (T)
Impulse durability (line-line)	C1 - 500 V / 250 A
	C3 - 70 A
Impulse durability (line-earth)	C1 - 500 V / 250 A
	C2 - 10 kV / 5 kA
	C3 - 50 A
	D1 - 500 A
Alternating current carrying capacity (line-earth)	5 A - 1 s

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (amsl)

Approvals

Conformity/Approvals

ATEX	Ex II 1 G Ex ia IIC T4...T6
	Ex II 1 D Ex iaD 20 T85 °C...135 °C
IECEx	Ga Ex ia IIC T4...T6
	Ex iaD 20 T85 °C...T135 °C

Standards and regulations

Standards/specifications	EN 61643-21
Note	A2:2013

LIT 2-12 - Surge protection device



2804694

<https://www.phoenixcontact.com/us/products/2804694>

Standards/specifications	EN 60079-0
Note	2018
Standards/specifications	EN 60079-11
Note	2012
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-11
Note	2011

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

LIT 2-12 - Surge protection device


2804694

<https://www.phoenixcontact.com/us/products/2804694>




Drawings

Circuit diagram



Dimensional drawing




LIT 2-12 - Surge protection device

2804694

<https://www.phoenixcontact.com/us/products/2804694>



Diagram



LIT 2-12 - Surge protection device



2804694

<https://www.phoenixcontact.com/us/products/2804694>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2804694>



EAC

Approval ID: RU C-DE.*09.B.00169



DNV GL

Approval ID: TAE00001N8



UL Listed

Approval ID: FILE E 138168



ATEX

Approval ID: KEMA 09ATEX0051 X



EAC Ex

Approval ID: RU C-DE.**87.B.00420



IECEX

Approval ID: IECEX KEM 09.0018X



CCC

Approval ID: 2020322316000816



NEPSI-EX

Approval ID: GYJ20.1176X



CCC

Approval ID: 2020322316000816



UKCA-EX

Approval ID: DEKRA 21UKEX0233 X

LIT 2-12 - Surge protection device



2804694

<https://www.phoenixcontact.com/us/products/2804694>

Classifications

ECLASS

ECLASS-11.0	27130807
ECLASS-13.0	27171501

ETIM

ETIM 9.0	EC000943
----------	----------

UNSPSC

UNSPSC 21.0	39121620
-------------	----------

LIT 2-12 - Surge protection device



2804694
<https://www.phoenixcontact.com/us/products/2804694>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c2fade0c-24d3-47cd-8898-a62630d4df93

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com