




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **70**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	70
Number of Rows	2
Board-to-Board Configuration	Parallel

Electrical Characteristics

Insulation Resistance	5000 MΩ
Operating Voltage	30 VAC

Body Features

PCB Retention Feature Material	Copper Alloy
PCB Retention Feature Plating Material	Tin over Nickel
Primary Product Color	Black

Contact Features

	150 μin
Mating Pin Diameter	.46 mm[.018 in]



PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Contact Type	Socket
Contact Current Rating (Max)	.5 A

Termination Features

Rectangular Termination Post & Tail Thickness	.08 mm[.003 in]
Rectangular Termination Post & Tail Width	.36 mm[.014 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

PCB Mount Retention Type	Hold-Down Post
Mating Alignment	With
Mating Alignment Type	Polarizing Tab
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	LCP - GF (Liquid Crystal Polymer)

Dimensions

Connector Height	4.75 mm[.187 in]
Row-to-Row Spacing	1.27 mm[.05 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0



Packaging Features

Packaging Quantity	10
Packaging Method	Box, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-104656-7
70 50/50 HDR DRST SFMNT.320 SN

TE Part # 5-104693-7
70 50/50 HDR DRST SFMNT.390 SN

TE Part # 5-104894-7
70 50/50 GRID RA HDR LF

TE Part # 5-104895-8
80 50/50 GRID RA HDR W/LTCH LF



TE Part # 5-104655-8
70 50/50 HDR DRST SFMNT TIN

TE Part # 5-104892-7
70 50/50 GRID RCPT W/LTCH LF

TE Part # 5-104895-7
70 50/50 GRID RA HDR W/LTCH LF

TE Part # 5-147383-7
70 50/50 HDR SMT.390 W/HD VC

TE Part # 5-147427-2
70 50/50 RCPT DRST SMT HD SN

TE Part # 5-1571424-8
70 50/50 HDR DRST TH TIN

TE Part # 5-2267255-7
70 50/50 HDR DRST TH.320 SN

TE Part # 5-2267256-7
70 50/50 HDR DRST TH.390 SN

TE Part # 5-2267258-7
70 50/50 HDR TH/PIP.250 W/HD SN

TE Part # 5-2267259-7
70 50/50 HDR TH/PIP.320 W/HD SN

TE Part # 5-2267260-7
70 50/50 HDR TH/PIP.390 W/HD VC

Also in the Series | AMPMODU 50/50 Grid

Connector Caps & Covers(9)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(299)

Ribbon Cable Connectors(34)

Customers Also Bought

TE Part #5747461-6
HD-20 RCPT 25P RA 590 FFSCRLK

TE Part #1-1757819-0
AMPLIMITE,ASY,PLUG,STD,109,ZN,5,CT

TE Part #5520257-2
MJ,TE,4P,PNL STOPS

TE Part #104257-2
03 MTE RCPT HSG SR LATCH .100





TE Part #2176245-9
CRGS1206 5% 4R7



TE Part #DT04-2P-E008
REC, 2P, GRY, N, XCAP



TE Part #0413-204-2005
SEALING PLUG, SIZE 20, RED



TE Part #5-5330808-6
SOCKET,MIN-SPR W/H SN-AU SER-1



TE Part #2129320-3
Mini Displayport Reverse Offset



TE Part #3-2176452-6
CPF 0201 1K24 0.1% 25ppm 1K RL

Documents

Product Drawings

70 50/50 GRID DRST SFMNT RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-104652-7_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-104652-7_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-104652-7_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION1AND2

English

Ribbon Cable Interconnect Solutions

English

Fine Pitch Stacking Connectors - 1.27mm AMPMODU 50/50 Grid Connectors

English

Product Specifications



Application Specification

English

Agency Approvals

UL Report

English