




Connectors > Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage**

Sealable: **No**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Data Rate (Max): **16 Gb/s**

Number of Ports: **5**

Features

Product Type Features

Cage Type	Single
Pluggable I/O Product Type	Cage
Sealable	No
Form Factor	SFP+

Configuration Features

Number of Ports	5
Port Matrix Configuration	1 x 5

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Contact Features

Tail Plating Material	Tin
-----------------------	-----

Termination Features

Termination Post & Tail Length	2.05 mm[.081 in]
Termination Method to PCB	Through Hole - Press-Fit

Housing Features



Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Enhanced
Heat Sink Compatible	Yes

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG	 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG
 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG
 TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG	 TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG	 TE Part # 2018002-6 KIT, SEATING TOOL, SFP+, 1X5	 TE Part # 2215058-5 ASSY, EXTRACT TL, SFP+ 1X5


Customers Also Bought

 TE Part #1888247-1 20 POS SMT CONN, SFP/SFP+, 30A	 TE Part #36189 BUDG R 22-16 COMM 22-18 MIL 4	 TE Part #1857657-1 Female Connector	 TE Part #2170703-7 CAGE ASSEMBLY, QSFP28 1X1, SPRING
--	---	--	---



TE Part #2007198-1

SFP+ 1x1 Cage Assembly, Press-




TE Part #1982738-1

Female Connector Telcordia



TE Part #2301997-7

RJ45 JACK INT.MAG. 1GB LED 2X1



TE Part #2288221-1

CFP2 EMI/DUST PLUG



TE Part #1393280-5

V23086C1001A402

Documents

Product Drawings

SFP+ ENHANCED 1X5 CAGE ASSEMBLY PRESS FI

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2284170-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2284170-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2284170-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773455-3 - Quick Reference Guide SFP+ Solutions

English

Product Specifications

Application Specification

English