



Connectors > Circular Connectors > Standard Circular Connectors > D38999: Square Flange, 25-35 insert



Connector System: **Cable-to-Panel**
Connector Mounting Type: **Panel Mount**
Number of Positions: **128**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**

[All D38999: Square Flange, 25-35 insert \(38\)](#)

Features

Product Type Features

Product Type	Connector Assembly
Assembly Type	Electrical Connector
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Square Flange Receptacle

Configuration Features

Keying & Polarized Position Locations	N
Factory Installed Backshell	No
Keying	Keyway Polarization N
Number of Positions	128
Number of Power Positions	0
Number of Signal Positions	128
Contacts Preloaded	No

Electrical Characteristics



Operating Voltage	400 VAC
Voltage	1300 Vrms

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	Yes
Feedthrough Type	No
Environmental Protection Type	Elastomer Sealed
Entry Style	Rear Insertion
Fluid Type	Coolanol 25, M2-V, MIL-DTL-5624 (JP-4,JP-5), MIL-DTL-83133 (JP-8), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I
Shell Plating Material	Cadmium, O.D.
Shell Base Material	Aluminum 6061-T6
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No

Contact Features

Contact Quantity (Size 22D)	128
Contact Current Rating (Max)	5 A
Reverse Gender	No
Contact Layout Arrangement	25 – 35
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention Type	Triple Start Threaded
Panel Mount Feature	With
Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	25
Alignment Keyed	Clocking

Dimensions

Compatible Insulation Diameter Range	.76 – 1.37 mm[.03 – .054 in]
Assembly Length	31.5 mm[1.24 in]
Wire Size	.08 – .33 mm ²

Usage Conditions

Fluid Resistance	Yes
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	Yes

Packaging Features

Packaging Quantity	1
--------------------	---

Other

Position Locations Omitted	All
----------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-D38999-DTS24U
D38999: Straight Plug, 25-35 Insert

Customers Also Bought

TE Part #208473-1
CMC RECEPTACLE ASSY,SIZE 28

TE Part #GA10K3A1AM
DISCRETE 10K, +/-0.05C FROM 32C to 44CTE Part #38943-16L
CONT SOC ASSYTE Part #YDTS20W13-35PNV001
RECP ASSYTE Part #YDTS20W15-35SNV001
RECP ASSYTE Part #ZPF00000000001904
182-0001-08TE Part #ABC03N-16S
IN-LINE RECPTE Part #YABC03N-163S000000
IN-LINE RECPTE Part #ZPF000000000102762
787-8055-10MTE Part #2560-214-1631
CONT PIN

Documents

Product Drawings
RECP ASSY



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS20W25-35SNV001_99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_YDTS20W25-35SNV001_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_YDTS20W25-35SNV001_99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS

English