




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **250 VAC**

Contact Retention Within Housing: **With**

Features

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Mating Pin Diameter	3.56 mm[.14 in]
Wire Contact Termination Area Plating Thickness	1 – 3 µm[39.37 – 118.11 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	17 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	With
Contact Retention Type Within Housing	Locking Lance
Dimensions	
Compatible Insulation Diameter Range	2.5 – 4.5 mm[.098 – .177 in]
Wire Size	2.1 – 5.3 mm²
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power
Packaging Features	
Packaging Quantity	2500
Packaging Method	Carton
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-480586-0 09P .140 MNL CAP NAT	 TE Part # 1-350347-0 03P .140 MNL CAP PM NAT	 TE Part # 1-480673-0 09P .140 MNL CAP PM NAT	 TE Part # 1-350345-0 02P .140 MNL CAP P/M NAT
 TE Part # 1-480512-0 04P .140 MNL CAP NAT	 TE Part # 794683-1 09P .140 MNL CAP BLK HT	 TE Part # 539764-1 EXTRACTION TOOL	 TE Part # 925450-1 M-N-L PIN HSG
 TE Part # 2151321-1 OCEAN_2.0_APPLICATOR-S-140F190O180F-SSM	 TE Part # 2151321-2 OCEAN_2.0_APPLICATOR-S-140F190O180F-SSA	 TE Part # 7-2151321-7 OCEAN_2.0_SPARE_PART_KIT-140F190O180F	 TE Part # 794061-1 03P .140 MNL CAP BLK HT

Also in the Series | 0.140 MATE-N-LOK

 Connector Contacts(13)	 Insertion & Extraction Tools(1)	 Rectangular Power Connectors(1)
----------------------------	-------------------------------------	-------------------------------------

Customers Also Bought






TE Part #1-1718491-1
1.5/2.8MMTAB HSG 25POS ASSY



TE Part #925712-1
.140 DIA SOCKET



TE Part #160915-2
250 FASTON,REC.,20-17 AWG,TPPB



TE Part #881775-1
ECONOSEAL, CONNECTOR HOUSING



TE Part #CH03056001
QSZH-125-NR4-75MM



TE Part #1-1718284-2
ADAPTER 90°FOR 10-14POS. SOCKE



TE Part #1337245-3
HSG ASSY DIA 1.5MM SOCKETLATCH



TE Part #927843-2
.140 SOCKET



TE Part #1544132-2
CLIP 6,3 SECU 0,35

Documents

Product Drawings

.140 DIA PIN

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_925713-2_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_925713-2_L.3d_igs.zip

English

Customer View Model

ENG_CVM_925713-2_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English