



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Tin-Lead over Nickel**
Operating Voltage: **300 VAC**
Compatible With Wire & Cable Type: **Discrete Wire**

Features

Product Type Features

Applied Pressure	Standard
------------------	----------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	300 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Contact Type	Socket
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Tin-Lead over Nickel
Contact Base Material	Copper Alloy



Contact Current Rating (Max)	3 A
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	With
Dimensions	
Compatible Insulation Diameter Range	.64 – 1.52 mm [.025 – .06 in]
Wire Size	394.71 – 1184.12 CMA
Usage Conditions	
Operating Temperature Range	-65 – 105 °C [-85 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
Compatible With Approved Standards Products	CSA LR7189, UL E28476
Packaging Features	
Packaging Quantity	15000
Packaging Method	Reel
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | AMPMODU IV/V



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(931)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(7)




Wire-to-Board Connector Assemblies & Housings(436)

Customers Also Bought



TE Part #5748677-1
PLTD PLST CBL CLMP KIT,SZ 1




TE Part #103669-1
02 MTE HDR SRST LATCH W/HLDWN



TE Part #102241-2
04 MODIV HG COMP SR .100 POL



TE Part #104257-5
06 MTE RCPT HSG SR LATCH .100



TE Part #103670-5
06 MTE HDR SRST LATCH W/HLDWN




TE Part #7-1879028-1
RN 0805 280K 0.1% 10PPM 1K RL



TE Part #796690-4
TERMI-BLOK PCB MOUNT 4P



TE Part #796690-6
TERMI-BLOK PCB MOUNT 6P



TE Part #87756-3
MOD IV RECP LP



TE Part #580317J001
V2-8.0-0-FSP-SM

Documents



Product Drawings

SHORT POINT CONT 30 DPLX STMPD

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_104479-4_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_104479-4_R.3d_igs.zip

English

Customer View Model

ENG_CVM_104479-4_R.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_104479-4_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_104479-4_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_104479-4_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English