

Sensors > Pressure Sensors > Pressure Transducers > Wireless Pressure Transducer



Pressure Sensor Type: Industrial Pressure Transducer, Wireless Pressure Transducer

Pressure: 20 bar [300 psi]

Pressure Type: Gauge

Frequency Band: 2400 MHz

Supply Voltage Range: 2.7 V

[All Wireless Pressure Transducer \(17\)](#)

Features

Product Type Features

Pressure Sensor Type

Industrial Pressure Transducer, Wireless Pressure Transducer

Pressure Type

Gauge

Configuration Features

Electrical Connection

No Connector

Electrical Characteristics

Supply Voltage Range

2.7 V

Signal Characteristics

Frequency Band

2400 MHz

Dimensions

Hex Width Across Flats

24 mm [.944 in]

Product Height

48.26 mm [1.9 in]

Usage Conditions

Pressure

20 bar [300 psi]

Operating Temperature Range

-20 – 85 °C [-4 – 185 °F]

Operation/Application

Output Signal Type	Bluetooth
Proof Pressure Range	2X Rated
Pressure Accuracy	±0.25% FSO

Other

Sensor Options	IP67 Protection
Port Fitting	1/4 MNPT

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.85% in 736 RED GLUE) <small>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-PTT0063
Wireless Pressure TransducerTE Part # M5254-000005-300PG
PRESS XDCR M5254-000005-300PG

Also in the Series | MEAS M5600



Pressure Transducers(17)

Customers Also Bought

TE Part #2176230-2
3522 1R0 5% 3WTE Part #6-2176459-3
SMW 7W 39R 5% TapedTE Part #1-726389-2
187 FASTON,FLAG,TAB,TPBRTE Part #2-321868-2
TERMINAL,SOLIS R UNPL 1/0 3/8TE Part #DT4P-L012-GKT
GASKET, 4P, BLK, DT/DTMTE Part #321871
BODY SOLIS RING 2/0 3/8TE Part #CSA-RPSM-216-RSFB
RP-SMA to RP-SMA 216mm RG174TE Part #5-2176474-4
RA73F 1J 1K96 0.1% 1K RLTE Part #1-2176475-5
RA73F 1J 8K25 0.1% 1K RLTE Part #EN9051-000
GUROFLEX-N-C1000

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_M5600-000005-300PG_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_M5600-000005-300PG_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_M5600-000005-300PG_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M5600](#)

English

Product Specifications

[Purchase Specification](#)

English