



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Tab**

Mating Tab Width: **1.6 mm [.063 in]**

Mating Tab Thickness: **.6 mm [.024 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **20 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(324\)](#)

Features

Product Type Features

|                         |               |
|-------------------------|---------------|
| Receptacle Style        | 180°          |
| Sealable                | Yes           |
| Primary Locking Feature | Locking Lance |

Body Features

|                    |                        |
|--------------------|------------------------|
| Terminal Seal Type | Single Wire Seal (SWS) |
|--------------------|------------------------|

Contact Features

|                                                |                  |
|------------------------------------------------|------------------|
| Contact Size                                   | 1.6mm            |
| Contact Fabrication                            | Stamped & Formed |
| Wire Contact Termination Area Plating Material | Tin              |
| Typical Current Rating                         | 10 A             |
| Crimp Type                                     | F-Crimp          |
| Terminal Type                                  | Tab              |
| Mating Tab Width                               | 1.6 mm[.063 in]  |
| Mating Tab Thickness                           | .6 mm[.024 in]   |
| Interface Plating                              | Gold (Au)        |

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|



|                                                                 |                                                                                                                                 |
|-----------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Product Terminates To                                           | Wire                                                                                                                            |
| Dimensions                                                      |                                                                                                                                 |
| Compatible Insulation Diameter Range                            | 1.4 – 2.1 mm[.055 – .083 in]                                                                                                    |
| Wire Size                                                       | .5 – 1 mm²                                                                                                                      |
| Wire Size Search                                                | 17 AWG, 18 AWG, 19 AWG, 20 AWG                                                                                                  |
| Tab Length                                                      | 22.4 mm[.88 in]                                                                                                                 |
| Usage Conditions                                                |                                                                                                                                 |
| Insulation Option                                               | Uninsulated                                                                                                                     |
| Operating Temperature (Max)                                     | 140 °C[284 °F]                                                                                                                  |
| Operating Temperature Range                                     | -40 – 140 °C[-40 – 284 °F]                                                                                                      |
| Operation/Application                                           |                                                                                                                                 |
| Conforms to KOMAX Automatic Component Insertion Guideline       | Yes, per Version 5.0 (March 2018)                                                                                               |
| Compatible With Wire Base Material                              | Copper                                                                                                                          |
| Industry Standards                                              |                                                                                                                                 |
| Compatible With Agency/Standards Products                       | DIN 72 551 Part 5 and 6                                                                                                         |
| Packaging Features                                              |                                                                                                                                 |
| Packaging Quantity                                              | 4000                                                                                                                            |
| Packaging Method                                                | Reel                                                                                                                            |
| Other                                                           |                                                                                                                                 |
| Terminal Transmits                                              | 0 – 24 A (Low Power)                                                                                                            |
| Product Compliance                                              |                                                                                                                                 |
| For compliance documentation, visit the product page on TE.com> |                                                                                                                                 |
| EU RoHS Directive 2011/65/EU                                    | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                                     | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016                   | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006                          | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                                                 | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                                       |                                                                                                                                                         |                                                                                                                                                            |                                                                                                                                                          |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # CAT-H3399-CH8172<br/>Heavy Duty Sealed Connector Series Housings</p> |  <p>TE Part # CAT-L489-CH8172<br/>LEAVYSEAL Connector Housings</p>   |  <p>TE Part # 963530-1<br/>EINZELLEITERDICHTNG</p>                    |  <p>TE Part # 539960-1<br/>AUSZ-WKZ,MICRO TIM.</p>                  |
|  <p>TE Part # 964972-1<br/>EINZELLEITERDICHTNG</p>                                 |  <p>TE Part # 9-2348782-1<br/>HD MATEnet 2+6 TAB HSG ASSY, GRP E</p> |  <p>TE Part # 9-2348792-1<br/>HD MATEnet 1+12 TAB HSG ASSY, GRP E</p> |  <p>TE Part # CAT-T4827-CH8172<br/>Timer Connector Housing</p>      |
|  <p>TE Part # 5-1579018-6<br/>INSERTION TOOL</p>                                   |  <p>TE Part # 1579008-9<br/>INSERTION TOOL</p>                       |  <p>TE Part # 2151057-1<br/>OCEAN_2.0_APPLICATOR-S-080F130O-RSM</p>   |  <p>TE Part # 2151057-2<br/>OCEAN_2.0_APPLICATOR-S-080F130O-RSA</p> |




TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp




TE Part # 5-2151057-1  
OCEAN\_2.0\_APPLICATOR-S-080F130O-RSM



TE Part # 5-2151057-2  
OCEAN\_2.0\_APPLICATOR-S-080F130O-RSA



TE Part # 7-2151057-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-080F130O




TE Part # 7-2151935-7  
OC-080F130O-752\_CRIMPTOOLINGKIT



TE Part # 9-2348782-2  
HD MATEnet 2+6 TAB HSG ASSY, GRP E



TE Part # 9-2348789-1  
HD MATEnet 2+6 TAB ASSY, GRP E, FLANGED




TE Part # 9-2348789-2  
HD MATEnet 2+6 TAB ASSY, GRP E, FLANGED


Also in the Series | Timer Connector System




Automotive Connector Caps & Covers (14)



Automotive Connector Locks & Position Assurance(15)




Automotive Housings(215)



Automotive Terminals(135)



Connector Seals & Cavity Plugs(38)




Crimp Terminal Housings(13)



Insertion & Extraction Tools(18)



Other Automotive Connector Accessories(1)




PCB Headers & Receptacles(40)



Quick Disconnects(4)

Customers Also Bought





TE Part #936462-2  
2.8MM SLD 2P CAP HSG




TE Part #969028-3  
TAB A 1.6x0.6 CONTACT CS SWS Au



ANVIL  
REPRESENTATION ONLY

TE Part #1803426-2  
ANVIL, COMBINATION, NO JOG, END FEED



TE Part #2-1633129-2  
ANVIL, COMBINATION .062



TE Part #2151224-1  
OCEAN\_2.0\_Applicator-S-062F110F-RSM



TE Part #2837157-1  
OCEAN\_2.0\_Applicator-S-110F155O-RSM



TE Part #7-568176-0  
CRIMPER, WIRE (.050" 'F')



TE Part #1801174-5  
2W TAB HP CONNECTOR GREEN



TE Part #CD41583001  
55E0211-0.50-0(B01)

TE Part #1-2429936-1  
5POS,MCON 1.2,TAB HSG ASSY,SLD, COD A

Documents

Product Drawings

TAB A 1.6x0.6 CONTACT CF SWS Au

English

TAB A 1.6x0.6 CONTACT CF SWS Au

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_964269-3\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_964269-3\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_964269-3\_E.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

HDSCS Catalog

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English