



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **In-Series Adapter**

Body Orientation: **Straight**

Side A Interface: **BNC**

Side A Gender: **Jack**

Side B Interface: **BNC**

Features

Product Type Features

Connector Interface Adapter Type	In-Series Adapter
Side A Interface	BNC
Side A Gender	Jack
Side B Interface	BNC
Side B Gender	Jack
Connector System	Cable-to-Cable
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Body Material	Zinc

Contact Features



RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Mechanical Attachment

Panel Attachment Style	Front Mount, Rear Mount
Connector Mounting Type	Panel Mount

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Grade	Commercial
Dielectric Material	Polyethylene

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-5227079-6
COMM BNC PLUG



TE Part # 5225395-1
BNC PLUG DUAL CRIMP RG58,A,B,C



TE Part # 5227079-5
COMM BNC PLUG



TE Part # 5225395-6
BNC PLUG DUAL CP RG142



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 2-5330061-1
BNC PLUG



TE Part # 5225395-8
BNC PLUG DUAL CRIMP RG179, 187



TE Part # 5413959-3
BNC HEX RT ANG PLUG 50 OHM



TE Part # 1-5221128-0
PLUG,COMMERCIAL BNC

Customers Also Bought





TE Part #2-6609107-0
PS0SXSS60=C1048



TE Part #862004-1
RECEPTACLE



TE Part #181953-1
250 FASTON,TAB,BR



TE Part #2-1419106-6
27E894=SOCKET,KH,14,SCW,POLY,N



TE Part #3-1618274-6
HC-3=RELAY, VACUUM, SPDT




TE Part #5536513-4
2MM FB,SIG,PIN,ASY,192,4.25



TE Part #865656-3
LGH 7 PIN MIN CIRC PLUG KIT



TE Part #1478769-4
ANTI-VIB NYLON GLD 20MM BLK



TE Part #862256-1
POTTING SHELL

Documents

Product Drawings
BNC BLKHD JACK ADAPTER GOLD
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_228226-1_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_228226-1_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_228226-1_F.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Product Specification

English

Product Specification

English