






◆FEATURES

- 1. Small in size and wide capacitance range. Max. 470µF is available.
- 2. Temperature characteristic is X7R in EIA code.
- 3. Superior humidity characteristic and long life.
- 4. Excellent high frequency characteristic due to low ESR.
- 5. High rated ripple current.
- 6. 250Vdc items are available.
- 7. Resin(UL94 V-0) used for coating.
- 8. Pb-free design(also ceramic dielectric)

APPLICATIONS

- 1. Smoothing circuit of switching mode AC-DC or DC-DC converter.
- 2. Noise suppressor for various kinds of equipments.
- 3. By-pass or decoupling circuits.
- 4. Automotive equipments.

◆CONSTRUCTION



◆RATINGS

Category Temperature Range	-55 to +125℃
2. Rated Voltage Range	25, 35, 50, 100, 250, 500Vdc
3. Rated Capacitance Range	0.1 to 470μF
4. Rated Capacitance Tolerance	M(±20%)
5. Temperature Characteristics	X7R
6. Rated Ripple Current	See No.5 on the following table

SPECIFICATIONS

No.	Items		Items Specification		Test Condition			
1	Withstand Between No abnormality. Voltage Terminals		Rated voltage		Withstand voltage			
		Terminals to		Less than 250V More than 250V Less than 500V More than 500V		250% of rated voltage		
		Coating Resin				100V + 150% of rated voltage		
						130% of rated voltage		
				Shall be applied for 5 seconds.				
2	2 Insulation Resistance		100/C _R (MΩ) or 4000(MΩ) whichever is less.	_	Rated voltage shall be applied for 60±5 seconds at temperature 25±2°C.			
3	3 Rated Capacitance		Rated Capacitance Within specified tolerance.		Cr≦10µF		Cr>10µF	
				Temperature	emperature 25±2°C		:2℃	
4	4 Dissipation Factor		Dissipation Factor 5.0% maximum.		1±0.1kHz		120±12Hz	
				Voltage	1±0.2Vrm	ıs	0.5±0.2Vrms	

As customer requirement, Chemi-Con has submits the test results according to AEC-Q200 for Multilayer ceramic capacitors. Please contact us for more information.







SPECIFICATIONS

No.	Items		Specification					
5	Rated Ripple Current		See STANDARD RATINGS	10kHz to 1MHz (sine curve) Ripple voltage Vp shall be less than the rated		e rated voltage.		
6	Robustness Tension of Terminations		No visible damage.	The force applied shall	be:			
				Lead φ (mm)	Tensile(N)	(sec.)		
	Terminations			0.5 max.	5	10±1		
				0.6 min. 10 10±		10±1		
		Bending		Lead φ (mm)	Bending(N)	(kg)		
				0.5 max.	2.5	0.25		
				0.6 min.	5	0.51		
				Time : 2times.				
7	Vibration		Appearance: No abnormality. Capacitance: To meet the initial specification. D.F.: To meet the initial specification.	Amplitude : 1.5mm Frequency range : 10-55-10Hz (1 min) Direction and time : 2 hours each to X, Y, Z axis. Total 6 hours.				
8	Solderability		Min. 75% of surface of the termination	Solder		Pb Free		
	,		shall be covered with new solder.	Solder Temperature		245±5℃		
				Dipping Time	±0.5sec.			
9	Resistance to Soldering Heat		Appearance : No abnormality. $\Delta C/C$: $\pm 15\%$ D.F. : To meet the initial specification. I.R. : To meet the initial specification.	Solder Temperature : 350±10°C Dipping Time : 3±0.5 sec. Depth : 1.5 to 2mm				
10	Temperature	Cycle	Step Temp	perature (°C)	(min.)			
			Appearance : No abnormality.	1 Min. Category temperature ±3 30±3				
		$\begin{array}{c} \Delta C/C:\pm 15\%\\ \text{D.F.}: \text{To meet the initial specification.}\\ \text{I.R.}: \text{To meet the initial specification.} \end{array}$		2 Room temperature 3 ma				
				3 Max. Category temperature ±3 30±3				
				4 Room	n temperature	3 max.		
				For 5 cycles for above temperature cycle.				
11	Humidity Load Life		Appearance : No abnormality. Δ C/C : \pm 20% D.F. : 10% maximum I.R. : 25/C _R (M Ω) or 1000(M Ω) whichever is less.	Temperature: 40±2°C Humidity: 90 to 95 Voltage: Rated voltage: 500± 24 0				
12	Endurance		Appearance : No abnormality. Δ C/C : \pm 20% D.F. : 10% maximum I.R. : 50/C _R (M Ω) or 1000(M Ω) whichever is less.	Temperature : 125±3°C Voltage : Rated vo Time : 1000± 4				

*CR : Rated Capacitance(µF)





STANDARD RATINGS

Rated voltage	Rated Capacitance	Dimensions (mm)					Maximum		Taping
(Vdc)	(μF)	Lmax.	Wmax.	Tmax.	F±0.8	φd±0.05	ripple current (Arms)	Part Number	Quantity per reel (pcs. / box)
	3.3	5.0	6.0	3.5	5.0	0.5	0.3	KTD250B335M32A0T00	2,000
	4.7	5.0	0.0	0.5	5.0	0.5	0.0	KTD250B475M32A0T00	2,000
	6.8							KTD250B685M43A0T00	2,000
	10	6.5	6.5	4.0	5.0	0.5	0.8	KTD250B106M43A0T00	2,000
	15							KTD250B156M43A0T00	2,000
	15							KTD250B156M55A0T00	2,000
	22	7.5	9.0	4.5	5.0	0.5	1.0	KTD250B226M55A0T00	2,000
25	33							KTD250B336M55A0T00	2,000
	47	10.0	11.5	5.5	5.0	0.5	1.5	KTD250B476M76A0T00	1,000
	68	13.5	15.0	6.0	10.0	0.6	2.0	KTD250B686M80A0B00	_
	100			8.0				KTD250B107M80A0B00	_
	150	22.5	20.0	6.0	20.0	0.8	3.0	KTD250B157M90A0B00	_
	220			8.0				KTD250B227M90A0B00	
	330	28.5	20.0	8.0	25.0	0.8	4.0	KTD250B337M99A0B00	_
	470			11.5				KTD250B477M99A0B00	2,000
	3.3	5.0	6.0	3.5	5.0	0.5	0.3	KTD350B335M32A0T00	2,000
	4.7 6.8							KTD350B475M32A0T00	
	10	6.5	6.5	4.0	5.0	0.5	0.8	KTD350B685M43A0T00 KTD350B106M43A0T00	2,000 2,000
35	15							KTD350B106M45A0T00	2,000
	22	7.5	9.0	4.5	5.0	0.5	1.0	KTD350B156M55A0T00	2,000
	33			5.0				KTD350B336M76A0T00	1,000
	47	10.0	11.5	5.5	5.0	0.5	1.5	KTD350B350M76A0T00	1,000
	1.0			5.5	+			KTD500B105M32A0T00	2,000
	1.5							KTD500B155M32A0T00	2,000
	2.2	5.0	6.0	3.5	5.0	0.5	0.3	KTD500B135M32A0T00	2,000
	3.3							KTD500B225M32A0T00	2,000
	4.7							KTD500B475M43A0T00	2,000
	6.8	6.5	6.5	4.0	5.0	0.5	0.8	KTD500B685M43A0T00	2,000
	10			1	 	<u> </u>		KTD500B106M55A0T00	2,000
50	15	7.5	9.0	4.5	5.0	0.5	1.0	KTD500B156M55A0T00	2,000
	22	10.0	11.5	5.0	5.0	0.5	1.5	KTD500B226M76A0T00	1,000
	33	13.5	15.0	5.5	10.0	0.6	2.0	KTD500B336M80A0B00	_
	47			6.0				KTD500B476M90A0B00	_
	68	22.5	20.0	6.0	20.0	0.8	3.0	KTD500B686M90A0B00	_
	100			7.0				KTD500B107M90A0B00	_
	150	28.5	20.0	7.5	25.0	0.8	4.0	KTD500B157M99A0B00	_
	220	20.5	20.0	10.0	25.0	0.8	4.0	KTD500B227M99A0B00	_
	0.33							KTD101B334M32A0T00	2,000
	0.47				5.0	0.5	0.3	KTD101B474M32A0T00	2,000
	0.68	5.0	6.0	3.5				KTD101B684M32A0T00	2,000
	1.0	5.0	0.0	0.5				KTD101B105M32A0T00	2,000
	1.5							KTD101B155M32A0T00	2,000
	2.2							KTD101B225M32A0T00	2,000
	1.5							KTD101B155M43A0T00	2,000
	2.2	6.5	6.5	4.0	5.0	0.5	0.8	KTD101B225M43A0T00	2,000
	3.3							KTD101B335M43A0T00	2,000
400	4.7					-		KTD101B475M43A0T00	2,000
100	3.3	7 -		4.5	F .	0.5	1.0	KTD101B335M55A0T00	2,000
	4.7	7.5	9.0		5.0	0.5	1.0	KTD101B475M55A0T00	2,000
	6.8 6.8	10.0	11.5	4.7 5.0	5.0	0.5	1.5	KTD101B685M55A0T00 KTD101B685M76A0T00	2,000 1,000
	10			5.0				KTD101B005M70A0100	1,000
	15	13.5	15.0	6.0	10.0	0.6	2.0	KTD101B106M80A0B00	_
	22					<u> </u>		KTD101B130M80A0B00 KTD101B226M90A0B00	_
	33	22.5	20.0	6.0	20.0	8.0	3.0	KTD101B336M90A0B00	_
	47			_				KTD101B330M30A0B00 KTD101B476M99A0B00	_
	68	28.5	20.0	7.5	25.0	0.8	4.0	KTD101B476M99A0B00	_
		20.0	1 -0.0		1 -0.0	1 0.0	1		





	0.1							KTD251B104M32A0T00	2,000
	0.15	5.0	6.0	3.5	5.0	0.5	0.3	KTD251B154M32A0T00	2,000
	0.22	5.0						KTD251B224M32A0T00	2,000
	0.33							KTD251B334M32A0T00	2,000
	0.47	0.5	0.5	4.0	F 0	0.5	0.0	KTD251B474M43A0T00	2,000
	0.68	6.5	6.5		5.0	0.5	0.8	KTD251B684M43A0T00	2,000
250	1.0	7.5	9.0	4.5	5.0	0.5	4.0	KTD251B105M55A0T00	2,000
230	1.5	7.5				0.5	1.0	KTD251B155M55A0T00	2,000
	2.2	10.0	11.5	6.0	5.0	0.5	1.5	KTD251B225M76A0T00	1,000
	2.2	13.5	15.0	5.0	10.0	0.6	2.0	KTD251B225M80A0B00	-
	3.3	22.5	20.0	6.0	20.0	0.8	3.0	KTD251B335M90A0B00	_
	4.7							KTD251B475M90A0B00	_
	6.8	28.5	20.0 7.5 29	7.5	25.0	0.8	4.0	KTD251B685M99A0B00	_
	10							KTD251B106M99A0B00	_
	15						KTD251B156M99A0B00	_	
	0.47	7.5	9.0	3.5	5.0	0.5	0.8	KTD501B474M55A0T00	2,000
500	0.56	1.5	9.0				0.8	KTD501B564M55A0T00	2,000
	0.68		11.5	3.4	5.0	0.5		KTD501B684M76A0T00	1,500
	1.0	10.0		3.8			1.0	KTD501B105M76A0T00	1,500
	1.2			4.2				KTD501B125M76A0T00	1,500

^{*}Please consult with us when you consider the rating other than a standard table.

◆PART NUMBERING SYSTEM ◆DIMENSIONS Crimped lead Straight lead K TD 500 B 106 M 55 A0 T 00 32 to 76 Size For all size Supplement code Taping code Terminal code Size code ≥ ≥ Capacitance tolerance code Nominal Capacitance code F Temperature characteristics code Rated voltage code Series code Category

Please refer to "Part Numbering System" of the beginning of a catalog for the details.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

United Chemi-Con (UCC):

KTD500B156M55A0T00	KTD251B684M43A0T00	KTD250B336M55A0T00	KTD101B474M32A0T00
KTD500B155M32A0T00	KTD500B157M99A0B00	KTD251B225M76A0T00	KTD501B684M76A0T00
KTD500B686M90A0B00	KTD251B475M90A0B00	KTD250B686M80A0B00	KTD501B105M76A0T00
KTD500B336M80A0B00	KTD251B335M90A0B00	KTD101B156M80A0B00	KTD501B125M76A0T00
KTD251B225M80A0B00	KTD101B155M43A0T00	KTD101B336M90A0B00	KTD101B686M99A0B00
KTD250B337M99A0B00	KTD251B106M99A0B00	KTD250B157M90A0B00	KTD250B156M43A0T00
KTD250B476M76A0T00	KTD101B685M76A0T00	KTD500B226M76A0T00	KTD500B476M90A0B00
KTD251B156M99A0B00	KTD501B564M55A0T00	KTD501B474M55A0T00	KTD500B107M90A0B00
KTD101B226M90A0B00	KTD101B476M99A0B00	KTD101B106M80A0B00	KTD250B107M80A0B00
KTD250B227M90A0B00	KTD250B477M99A0B00	KTD101B335M55A0T00	KTD250B156M55A0T00
KTD251B334M32A0T00	KTD251B685M99A0B00	KTD101B107M99A0B00	KTD500B227M99A0B00
KTD101B335M43A0T00	KTD500B685M43A0T00	KTD250B685M43A0T00	KTD101B684M32A0T00
KTD500B225M32A0T00	KTD251B154M32A0T00	KTD251B224M32A0T00	KTD500B335M32A0T00