



Part Number : [334721354](#)
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, with Clipslot, without Connector Position Assurance, Black, Terminals 1-5 and 8-12 Plugged
Series Number : 33472
Status : Active
Product Category : Connector Housings
Engineering Number : CVP33472-1354



Documents & Resources

Drawings
[334721354_sd.pdf](#)

Specifications
[AS-33472-100-CH-001.pdf](#)
[AS-33611-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, with Clipslot, without Connector Position Assurance, Black, Terminals 1-5 and 8-12 Plugged
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	884982644632

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	16.000/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm

Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>